


COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.19 ±0.03
A2	0.45 REF
A3	0.025 BASIC
b	∅0.27 ±0.03
D1	2.00 BASIC
E1	2.00 BASIC
e	0.40 BASIC
SD	0.20 BASIC
SE	0.20 BASIC

PKG. CODE	E	D	DEPOPULATED BUMPS
W362A2+2	2.48±0.06	2.48±0.06	NONE
W362A2+3	2.785±0.055	2.785±0.055	NONE
W362B2+1	2.838 ±0.025	2.838 ±0.025	NONE
W362A2+1	2.57±0.10	2.57±0.10	NONE



NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -

 <b>maxim integrated™</b>			
TITLE PACKAGE OUTLINE 36 BUMPS WLP PKG. 0.40mm PITCH			
APPROVAL TIE WANG 12/19/12	DOCUMENT CONTROL NO. 21-0457	REV. E	1/1