



TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64±0.05
A1	0.16±0.03
A2	0.48 REF
A3	0.025 BASIC
A4	0.07 BASIC
b	∅0.21±0.03
D1	1.20 BASIC
E1	1.20 BASIC
e	0.30 BASIC
SD	0.00 BASIC
SE	0.00 BASIC

PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W251A1+1	1.56	1.60	1.56	1.60	NONE



BOTTOM VIEW

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeters.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02mm unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.



TITLE: PACKAGE OUTLINE 25 BUMPS, WLP PKG. 0.3mm PITCH			
APPROVAL TIE WANG 02/09/10	DOCUMENT CONTROL NO. 21-0483	REV. B	1/1

-DRAWING NOT TO SCALE-