



COMMON DIMENSIONS	
A	0.76 ±0.05
A1	0.19 ±0.03
A2	0.57 REF
A3	0.040 BASIC
b	∅0.27 ±0.03
D1	5.60 BASIC
E1	5.60 BASIC
e	0.40 BASIC
SD	0.00 BASIC
SE	0.00 BASIC



PKG. CODE	VARIABLE DIMENSIONS		DEPOPULATED BUMPS
	D	E	
W2256B6+1	6.485 ±0.015	6.485 ±0.015	NONE
W2256C6+1	6.405 ±0.015	6.405 ±0.015	NONE
W2256D6+1	6.308 ±0.025	6.217 ±0.025	NONE



- NOTES:
1. Terminal pitch is defined by terminal center to center value.
 2. Outer dimension is defined by center lines between scribe lines.
 3. All dimensions in millimeter.
 4. Marking shown is for package orientation reference only.
 5. Tolerance is ± 0.02 unless specified otherwise.
 6. All dimensions apply to PbFree (+) package codes only.
 7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -


maxim integrated™

TITLE PACKAGE OUTLINE 225 BUMPS
WLP PKG. 0.4 mm PITCH,

APPROVAL	DOCUMENT CONTROL NO. 21-0543	REV. E	1/1
----------	---------------------------------	-----------	-----