


COMMON DIMENSIONS	
A	0.75 ±0.05
A1	0.19 ±0.03
A2	0.56 REF
A3	0.040 BASIC
b	∅0.27 ±0.03
D1	1.60 BASIC
E1	2.40 BASIC
e	0.40 BASIC
SD	0.00 BASIC
SE	0.00 BASIC



PKG. CODE	E		D		DEPOPULATED BUMPS
	MIN	MAX	MIN	MAX	
W352B3+1	3.11	3.14	2.30	2.33	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -

MAXIM			
TITLE		PACKAGE OUTLINE, 35 BUMPS WLP PKG. 0.40mm PITCH	
APPROVAL TIE WANG 2/20/12	DOCUMENT CONTROL NO. 21-0611	REV. B	1/1