


COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.17 ±0.03
A2	0.47 REF
A3	0.025 BASIC
b	∅0.25 ±0.03
D1	1.40 BASIC
E1	1.40 BASIC
e	0.35 BASIC
SD	0.00 BASIC
SE	0.00 BASIC

PKG. CODE	E	D	DEPOPULATED BUMPS
W251A2+1	1.995 ±0.015	1.945 ±0.015	NONE
W252B2+2	2.118 ±0.025	2.118 ±0.025	NONE



- NOTES:
1. Terminal pitch is defined by terminal center to center value.
 2. Outer dimension is defined by center lines between scribe lines.
 3. All dimensions in millimeter.
 4. Marking shown is for package orientation reference only.
 5. Tolerance is ± 0.02 unless specified otherwise.
 6. All dimensions apply to PbFree (+) package codes only.
 7. Front - side finish can be either Black or Clear.

maxim integrated™			
TITLE		PACKAGE OUTLINE, 25 BUMPS WLP PKG. 0.35 mm PITCH	
APPROVAL TIE WANG 3/7/13	DOCUMENT CONTROL NO. 21-0630	REV. B	1/1