



TOP VIEW



SIDE VIEW

COMMON DIMENSIONS	
A	0.64 ±0.05
A1	0.19 ±0.03
A2	0.45 REF
A3	0.04 BASIC
b	∅0.27 ±0.03
D1	2.40 BASIC
E1	2.80 BASIC
e	0.40 BASIC
SD	0.00 BASIC
SE	0.20 BASIC



BOTTOM VIEW

PKG. CODE	E	D	DEPOPULATED BUMPS
W563D3-1	3.665 ±0.015	3.205 ±0.015	NONE
W563E3-1	3.545 ±0.015	3.245 ±0.015	NONE
W562A3+1	3.297 ±0.025	2.897 ±0.025	NONE

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -

			
TITLE PACKAGE OUTLINE 56 BUMPS WLP PKG. 0.40mm PITCH			
APPROVAL	DOCUMENT CONTROL NO.	REV.	
	21-0672	C	1/1