



TOP VIEW



SIDE VIEW

| COMMON DIMENSIONS | |
|-------------------|-------------|
| A | 0.76 ±0.05 |
| A1 | 0.19 ±0.03 |
| A2 | 0.57 REF |
| A3 | 0.025 BASIC |
| b | ∅0.27 ±0.03 |
| D1 | 5.20 BASIC |
| E1 | 5.20 BASIC |
| e | 0.40 BASIC |
| SD | 0.20 BASIC |
| SE | 0.20 BASIC |



BOTTOM VIEW

| PKG. CODE | E | D | DEPOPULATED BUMPS |
|-----------|--------------|--------------|-------------------|
| W1965B5+1 | 5.858 ±0.025 | 5.787 ±0.025 | NONE |
| W1965C5+1 | 5.958 ±0.025 | 5.867 ±0.025 | NONE |

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -

| | | |
|--|---------------------------------|---------------|
|  maxim integrated™ | | |
| TITLE PACKAGE OUTLINE 196 BUMPS WLP PKG. 0.40mm PITCH | | |
| APPROVAL TIE WANG 6/18/13 | DOCUMENT CONTROL NO. 21-0682 | REV. B 1/1 |