






TOP VIEW




see Note 7

FRONT VIEW

COMMON DIMENSIONS	
A	0.65 MAX
A1	0.19±0.03
A2	0.40 REF
A3	0.040 BASIC
b	∅0.27±0.03
D	3.208±0.025
E	3.208±0.025
D1	2.40 BASIC
E1	2.40 BASIC
e	0.40 BASIC
SD	0.00 BASIC
SE	0.00 BASIC
DEPOPULATED BUMPS: NONE	



SIDE VIEW



BOTTOM VIEW

NOTES:

1. Terminal pitch is defined by terminal center to center value.
2. Outer dimension is defined by center lines between scribe lines.
3. All dimensions in millimeter.
4. Marking shown is for package orientation reference only.
5. Tolerance is ± 0.02 unless specified otherwise.
6. All dimensions apply to PbFree (+) package codes only.
7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -



TITLE PACKAGE OUTLINE 49 BUMPS
WLP PKG 0.40mm PITCH, W493F3+1

APPROVAL
Saurabh Athavale
02/20/2014

DOCUMENT CONTROL NO.
21-0751

REV.
B 1/1