



COMMON DIMENSIONS	
A	0.47 ±0.04
A1	0.12 ±0.03
A2	0.35 REF
A3	0.04 BASIC
b	NA ±0.03
D	0.927 ±0.025
E	1.727 ±0.025
D1	NA BASIC
E1	1.244 BASIC
e	1.244 BASIC
SD	0.000 BASIC
SE	0.622 BASIC



- NOTES:
1. Terminal pitch is defined by terminal center to center value.
 2. Outer dimension is defined by center lines between scribe lines.
 3. All dimensions in millimeter.
 4. Marking shown is for package orientation reference only.
 5. Tolerance is ± 0.02 unless specified otherwise.
 6. All dimensions apply to PbFree (+) package codes only.
 7. Front - side finish can be either Black or Clear.

- DRAWING NOT TO SCALE -



TITLE		
PACKAGE OUTLINE, 2 BUMPS WLP PKG. 1.244mm PITCH, W20A1+3		
APPROVAL	DOCUMENT CONTROL NO.	REV.
	21-100010	A 1/1