

PCN NUMBER:09\_0032

PCN TITLE: AD5628/AD5648/AD5668 Datasheet Specification Change

From: REFERENCE CURRENT 40 TYP 50 MAX uA VREF=VDD=5.5V (per DAC channel)  
To: REFERENCE CURRENT 40 TYP 55 MAX uA VREF=VDD=5.5V (per DAC channel)

From: IDD(NORMAL MODE) VDD=4.5V to 5.5V TYP 2 MAX 2.5 mA INTERNAL REFERENCE  
ON  
To: IDD(NORMAL MODE) VDD=4.5V to 5.5V TYP 2 MAX 2.6 mA INTERNAL REFERENCE ON

From:IDD(NORMAL MODE) VDD=2.7V to 3.6V TYP 1.2 MAX 1.5 mA INTERNAL REFERENCE  
OFF  
To: IDD(NORMAL MODE) VDD=2.7V to 3.6V TYP 1.2 MAX 1.7 mA INTERNAL REFERENCE  
OFF

From: IDD(NORMAL MODE) VDD=2.7V to 3.6V TYP 1.7 MAX 2.25 mA INTERNAL  
REFERENCE ON  
To: IDD(NORMAL MODE) VDD=2.7V to 3.6V TYP 1.7 MAX 2.6 mA INTERNAL REFERENCE  
ON

From: REFERENCE CURRENT 40 TYP 50 MAX uA VREF=VDD=3.6V (per DAC channel)  
To: REFERENCE CURRENT 40 TYP 55 MAX uA VREF=VDD=3.6V (per DAC channel)