

AD623 Qualification Data

QUALIFICATION RESULTS			
TEST	CONDITIONS	SAMPLE SIZE	RESULTS
High Temperature Operating Life (HTOL)*	JEDEC <i>JESD22-A108</i>	9 lots 45	Pass
Highly Accelerated Stress Test (HAST)*	JEDEC <i>JESD22-A110</i>	9 lots of 45	Pass
Temperature Cycle (TC)*	JEDEC <i>JESD22-A104</i>	9 lots of 45	Pass
Autoclave (AC)*	JEDEC <i>JESD22-A102</i>	9 lots of 45	Pass
High Temperature Storage Life (HTSL)	JEDEC <i>JESD22-A103</i>	3 lots of 45	Pass
Solder Heat Resistance (SHR)*	<i>ADI-0049</i>	1 lot of 30	Pass
Latch-Up	JEDEC <i>JESD78</i>	6	Pass
Electrostatic Discharge <i>Human Body Model</i>	ESDA/JEDEC <i>JDS-001-2011</i>	3/voltage	Pass 3500V
Electrostatic Discharge <i>Field-Induced Charged Device Model</i>	JEDEC <i>JESD22-C101</i>	3/voltage	Pass 1250V

*Preconditioned per JEDEC/IPC J-STD-020 MSL 1