

PCN 12_0014		Detailed Specification Changes	
	Temp	From ( $\Omega$ )	To ( $\Omega$ )
<b>Vdd = 2.7V to 3.6V</b>			
On Resistance, $R_{on}$ (max)	+25C:	0.65	0.8
	-40C to +85C:	0.7	0.85
On Resistance match between channels (max)	-40C to +85C:	0.02	0.04
<b>Vdd = 2.5V</b>			
On Resistance, $R_{on}$ (max)	+25C:	0.78	0.95
	-40C to +85C:	0.83	1.0
On Resistance match between channels (max)	-40C to +85C:	0.01	0.04
On Resistance Flatness (max)	-40C to +85C:	0.3	0.35
<b>Vdd = 1.65V to 1.95V</b>			
On Resistance, $R_{on}$ (max) (1.8V)	+25C:	1.7	2
	-40C to +85C:	2.1	2.4
On Resistance, $R_{on}$ (max) (1.65V)	+25C:	2.5	3.1
	-40C to +85C:	3	3.6