

Table 1. Interface Timing Corrections

Parameter	Current Data Sheet Specification	Corrected Data Sheet Specification	Unit	Description
t ₇	50	140	ns min	Minimum SYNC high time in readback mode
t ₁₀	30	36	ns max	24 th SCLK falling edge to BUSY falling edge
t ₁₄	2000	100/2000	ns min/max	BUSY rising edge to DAC output response time