



# 产品认证证书

证书编号: CQC14001114900

## 申请人名称及地址

亚德诺半导体技术(上海)有限公司  
上海市浦东新区张江高科技园区祖冲之路2290号展想广场5楼

## 制造商名称及地址

Analog Devices  
804 Woburn Street Wilmington MA 美国

## 生产企业名称及地址

Analog Devices Gen. Trias (V018387)  
Gateway Business Park, Javalera, Geb. Trias, Cavite, 菲律宾

## 产品名称和系列、规格、型号

数字隔离器

ADUM1400ARW, ADUM1400ARWZ, ADUM1400BRW, ADUM1400BRWZ, ADUM1400CRW, ADUM1400CRWZ, ADUM1400SRWZ, ADUM1400WTRWZ,  
ADUM1401ARW, ADUM1401ARWZ, ADUM1401BRW, ADUM1401BRWZ, ADUM1401CRW, ADUM1401CRWZ, ADUM1401SRWZ, ADUM1401WTRWZ,  
ADUM1402ARW, ADUM1402ARWZ, ADUM1402BRW, ADUM1402BRWZ, ADUM1402CRW, ADUM1402CRWZ, ADUM1402SRWZ, ADUM1402WTRWZ,  
ADUM1300ARW, ADUM1300ARWZ, ADUM1300BRW, ADUM1300BRWZ, ADUM1300CRW, ADUM1300CRWZ, ADUM1300SRWZ, ADUM1300WTRWZ, ADUM1301ARW,  
ADUM1301ARWZ, ADUM1301BRW, ADUM1301BRWZ, ADUM1301CRW, ADUM1301CRWZ, ADUM1301SRWZ, ADUM1301WTRWZ 产品的额定值: 外部  
爬电距离: 7.7mm, 通过热循环测试, 基本或附加绝缘, 最大工作电压: 415V 有效值, 588V 峰值

## 产品标准和技术要求

GB4943.1-2011

## 认证模式

产品型式试验+初次工厂检查+获证后监督

上述产品符合CQC11-471543-2012认证规则的要求, 特发此证。

发证日期: 2014年09月10日

证书有效期内本证书的有效性依据发证机构的定期监督获得保持。

主任: \_\_\_\_\_



# 中国质量认证中心

中国·北京·南四环西路188号9区100070

<http://www.cqc.com.cn>

C 0056425



# PRODUCT CERTIFICATE

No.: CQC14001114900

## NAME AND ADDRESS OF THE APPLICANT

Analog Devices (Shanghai) Co.,Ltd.  
5F, Sandhill Plaza,2290 Zuchongzhi Road Zhangjiang Hi-Tech Park,Pudong New District,Shanghai,China

## NAME AND ADDRESS OF THE MANUFACTURER

Analog Devices  
804 Woburn StreetWilmingtonMA, USA

## NAME AND ADDRESS OF THE FACTORY

Analog Devices Gen. Trias (V018387)  
Gateway Business Park,Javalera, Geb. Trias,Cavite, Philippines

## NAME, MODEL AND SPECIFICATION

Digital Isolator

ADUM1400ARW, ADUM1400ARWZ, ADUM1400BRW, ADUM1400BRWZ, ADUM1400CRW, ADUM1400CRWZ, ADUM1400WSRWZ, ADUM1400WTRWZ, ADUM1401ARW, ADUM1401ARWZ, ADUM1401BRW, ADUM1401BRWZ, ADUM1401CRW, ADUM1401CRWZ, ADUM1401WSRWZ, ADUM1401WTRWZ, ADUM1402ARW, ADUM1402ARWZ, ADUM1402BRW, ADUM1402BRWZ, ADUM1402CRW, ADUM1402CRWZ, ADUM1402WSRWZ, ADUM1402WTRWZ, ADUM1300ARW, ADUM1300ARWZ, ADUM1300BRW, ADUM1300BRWZ, ADUM1300CRW, ADUM1300CRWZ, ADUM1300WSRWZ, ADUM1300WTRWZ, ADUM1301ARW, ADUM1301ARWZ, ADUM1301BRW, ADUM1301BRWZ, ADUM1301CRW, ADUM1301CRWZ, ADUM1301WSRWZ, ADUM1301WTRWZ 产品的额定值: 外部爬电距离: 7.7mm, 通过热循环测试, 基本或附加绝缘, 最大工作电压: 415V 有效值, 588V 峰值

## THE STANDARDS AND TECHNICAL REQUIREMENTS FOR THE PRODUCTS

GB4943.1-2011

## CERTIFICATION MODEL

Type Testing of Product + Initial Factory Inspection + Follow up Factory Inspection

This is to certify that the above mentioned products have met the requirements of certification rules CQC11-471543-2012.

Date of issue: Sep.10,2014

Validity of this certificate is subject to positive result of the regular follow up inspection by issuing certification body until the expiry date.

President:

  
Wang Kejiao



# CHINA QUALITY CERTIFICATION CENTRE

Section 9, No.188, Nansihuan Xilu, Beijing 100070 P.R.China  
<http://www.cqc.com.cn>

C 0056425