

U?		LTM4612_EV_REV_0		05-11-0058	
G12	PGOOD	A1	VIN	VOUT	J1
A12	MPGM	A2	VIN_1	VOUT_1	J2
B11	MPGM_1	A3	VIN_2	VOUT_2	J3
A7	INTVCC	A4	VIN_3	VOUT_3	J4
C12	MARG0	A5	VIN_4	VOUT_4	J5
C11	MARG1	A6	VIN_5	VOUT_5	J6
D12	MARG1_1	B1	VIN_6	VOUT_6	J7
C10	DRVCC	B2	VIN_7	VOUT_7	J8
E11	DRVCC_1	B3	VIN_8	VOUT_8	J9
E12	DRVCC_2	B4	VIN_9	VOUT_9	J10
B12	FSET	B5	VIN_10	VOUT_10	J11
A11	COMP	B6	VIN_11	VOUT_11	K1
D11	COMP_1	C1	VIN_12	VOUT_12	K2
J12	MTP1	C2	VIN_13	VOUT_13	K3
K12	MTP2	C3	VIN_14	VOUT_14	K4
L12	MTP3	C4	VIN_15	VOUT_15	K5
B7	VD	C5	VIN_16	VOUT_16	K6
C7	VD_1	C6	VIN_17	VOUT_17	K7
M12	FCB			VOUT_18	K8
F12	VFB			VOUT_19	K9
A8	PLLIN			VOUT_20	K10
A9	TRACK/SS			VOUT_21	K11
A10	RUN			VOUT_22	L1
B9	RUN_1			VOUT_23	L2
				VOUT_24	L3
				VOUT_25	L4
				VOUT_26	L5
				VOUT_27	L6
				VOUT_28	L7
				VOUT_29	L8
				VOUT_30	L9
				VOUT_31	L10
				VOUT_32	L11
				VOUT_33	M1
				VOUT_34	M2
				VOUT_35	M3
				VOUT_36	M4
				VOUT_37	M5
				VOUT_38	M6
				VOUT_39	M7
				VOUT_40	M8
				VOUT_41	M9
				VOUT_42	M10
				VOUT_43	M11
				VOUT_44	
D9	SGND				
H12	SGND_1				
D1	PGND				
D2	PGND_1				
D3	PGND_2				
D4	PGND_3				
D5	PGND_4				
D6	PGND_5				
E1	PGND_6				
E2	PGND_7				
E3	PGND_8				
E4	PGND_9				
E5	PGND_10				
E6	PGND_11				
E7	PGND_12				
E8	PGND_13				
F1	PGND_14				
F2	PGND_15				
F3	PGND_16				
F4	PGND_17				
F5	PGND_18				
F6	PGND_19				
F7	PGND_20				
F8	PGND_21				
F9	PGND_22				
G1	PGND_23				
G2	PGND_24				
G3	PGND_25				
G4	PGND_26				
G5	PGND_27				
G6	PGND_28				
G7	PGND_29				
G8	PGND_30				
G9	PGND_31				
G10	PGND_32				
G11	PGND_33				
H1	PGND_34				
H2	PGND_35				
H3	PGND_36				
H4	PGND_37				