



### Electrical Properties:

Frequency Range: 2.4~2.5 GHz  
 Impedance: 50Ω nominal  
 VSWR: <2.0:1  
 Gain: 2 dBi  
 Radiation: Omni  
 Polarization: Vertical

### Mechanical Properties:

Connector: MMCX right angle plug  
 Material:  
   Cable: RG178 coaxial  
   CAP: Polyurethane(Black)  
   Antenna Body: Brass with silver plating  
 Operation Temp.: -20°C to +65°C  
 Storage Temp.: -30°C to +75°C

RMM R/A  
Plug

TITLE	2.4Hz Antenna with CAP Customer Model	Rev. Date	Sheet
		10/23/06	1 of 1
UNIT	DWG. NO.	S152CL-03251	
mm			
SCALE			
NONE			

**NEARSON**