



Electrical Properties:

Frequency Range:	2.4~2.5 GHz
Impedance:	50Ω nominal
VSWR:	<2.0:1
Gain:	2 dBi
Radiation:	Omni
Polarization:	Vertical
Wave:	Half Wave Dipole

Mechanical Properties:

Material:	
Whip:	Polyurethane(Black)
Swivel Mechanism:	Polycarbonate(Black)
Connector:	Brass with black chrome plating
Operation Temp.:	-20°C to +65°C
Storage Temp.:	-30°C to +75°C

This is a RoHS compliant product.

TITLE	2.4GHz Swivel Antenna-181 Model		Rev. Date	SHEET
			01/22/06	1 of 2
UNIT	DWG. NO.	S181XX - 2450S		
in.(mm)				
SCALE				
1:1				

NEARSON