

Component Definition for: "ADSP-21569WCBCZ8"	
Number of Pins: 400	Number of Gates: 12
Name of Pattern: BC_400_3	Number of pattern Pins: 400
Symbol gating Information:	
Symbol name for gate 1 is ADSP-21569WCBCZ8_A	
Symbol name for gate 2 is ADSP-21569WCBCZ8_B	
Symbol name for gate 3 is ADSP-21569WCBCZ8_C	
Symbol name for gate 4 is ADSP-21569WCBCZ8_D	
Symbol name for gate 5 is ADSP-21569WCBCZ8	
Symbol name for gate 6 is ADSP-21569WCBCZ8_04	
Symbol name for gate 7 is ADSP-21569WCBCZ8_05	
Symbol name for gate 8 is ADSP-21569WCBCZ8_06	
Symbol name for gate 9 is ADSP-21569WCBCZ8_00	
Symbol name for gate 10 is ADSP-21569WCBCZ8_01	
Symbol name for gate 11 is ADSP-21569WCBCZ8_02	
Symbol name for gate 12 is ADSP-21569WCBCZ8_03	

Pin Data:		
Pin Number	Pin Name	Gate Number
Y8	DAI0_PIN01	1

Sym
F

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
V9	DAI0_PIN02	1
W9	DAI0_PIN03	1
Y9	DAI0_PIN04	1
W10	DAI0_PIN05	1
V10	DAI0_PIN06	1
Y10	DAI0_PIN07	1
W11	DAI0_PIN08	1
V11	DAI0_PIN09	1
Y11	DAI0_PIN10	1
Y12	DAI0_PIN11	1
W12	DAI0_PIN12	1
W13	DAI0_PIN19	1
V12	DAI0_PIN20	1
W18	DAI1_PIN20	1
V17	DAI1_PIN19	1
V20	DAI1_PIN12	1
V19	DAI1_PIN11	1
U18	DAI1_PIN10	1

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
T18	DAI1_PIN09	1
R19	DAI1_PIN08	1
U19	DAI1_PIN07	1
T19	DAI1_PIN06	1
U20	DAI1_PIN05	1
T20	DAI1_PIN04	1
R18	DAI1_PIN03	1
P18	DAI1_PIN02	1
R20	DAI1_PIN01	1
D19	DMC0_A00	2
D20	DMC0_A01	2
C20	DMC0_A02	2
C19	DMC0_A03	2
A19	DMC0_A04	2
B20	DMC0_A05	2
B18	DMC0_A06	2
A18	DMC0_A07	2
A16	DMC0_A08	2

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
B16	DMC0_A09	2
A15	DMC0_A10	2
B15	DMC0_A11	2
B14	DMC0_A12	2
A14	DMC0_A13	2
A13	DMC0_A14	2
B13	DMC0_A15	2
B17	DMC0_BA0	2
A17	DMC0_BA1	2
E19	DMC0_BA2	2
A5	DMC0_DQ15	2
B5	DMC0_DQ14	2
B6	DMC0_DQ13	2
B3	DMC0_DQ12	2
A2	DMC0_DQ11	2
A3	DMC0_DQ10	2
D3	DMC0_DQ09	2
C2	DMC0_DQ08	2

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
D1	DMC0_DQ07	2
E2	DMC0_DQ06	2
E1	DMC0_DQ05	2
G1	DMC0_DQ04	2
H1	DMC0_DQ03	2
G2	DMC0_DQ02	2
J1	DMC0_DQ01	2
J2	DMC0_DQ00	2
F2	DMC0_LDQS	3
F1	*DMC0_LDQS	3
G20	DMC0_VREF0	3
J4	DMC0_VREF1	3
B4	DMC0_UDQS	3
A4	*DMC0_UDQS	3
G19	DMC0_RZQ	3
A12	*DMC0_WE	3
A6	DMC0_UDM	3
B12	*DMC0_RESET	3

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
F19	*DMC0_RAS	3
H19	DMC0_ODT	3
C1	DMC0_LDM	3
F20	*DMC0_CS0	3
H20	DMC0_CKE	3
J19	*DMC0_CK	3
J20	DMC0_CK	3
E20	*DMC0_CAS	3
N3	PA_00	4
P3	PA_01	4
P2	PA_02	4
R3	PA_03	4
R1	PA_04	4
T2	PA_05	4
T3	PA_06	4
V1	PA_07	4
U3	PA_08	4
V2	PA_09	4

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
U2	PA_10	4
V8	PA_11	4
W6	PA_12	4
Y6	PA_13	4
W7	PA_14	4
W8	PA_15	4
W14	PB_15	4
Y14	PB_14	4
W5	PB_13	4
V7	PB_12	4
Y4	PB_11	4
Y3	PB_10	4
V6	PB_09	4
W3	PB_08	4
W4	PB_07	4
V5	PB_06	4
C8	PB_05	4
B7	PB_04	4

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
C7	PB_03	4
B8	PB_02	4
C9	PB_01	4
A7	PB_00	4
B11	JTG_TCK	5
C13	JTG_TDI	5
C12	JTG_TMS	5
A10	*JTG_TRST	5
B10	SYS_BMODE0	10
B9	SYS_BMODE1	10
A8	SYS_BMODE2	10
N1	SYS_CLKIN0	10
A11	*SYS_FAULT	10
A9	*SYS_HWRST	10
C10	*SYS_RESOUT	10
N19	HADC0_VIN0	11
N20	HADC0_VIN1	11
M19	HADC0_VIN2	11

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
M20	HADC0_VIN3	11
L18	HADC0_VREFN	11
L20	HADC0_VREFP	11
Y18	PC_07	12
W17	PC_06	12
V14	PC_05	12
Y17	PC_04	12
W16	PC_03	12
Y15	PC_02	12
W15	PC_01	12
V13	PC_00	12
L1	SYS_XTAL0	10
M3	SYS_CLKOUT	10
C11	JTG_TDO	5
L19	VDD_ANA	6
F6	VDD_DMC	6
F7	VDD_DMC	6
F8	VDD_DMC	6

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
F9	VDD_DMC	6
F10	VDD_DMC	6
F11	VDD_DMC	6
F12	VDD_DMC	6
F13	VDD_DMC	6
F14	VDD_DMC	6
F15	VDD_DMC	6
G6	VDD_DMC	6
G7	VDD_DMC	6
G8	VDD_DMC	6
G9	VDD_DMC	6
G12	VDD_DMC	6
G13	VDD_DMC	6
G14	VDD_DMC	6
G15	VDD_DMC	6
H6	VDD_DMC	6
H7	VDD_DMC	6
H14	VDD_DMC	6

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
H15	VDD_DMC	6
J6	VDD_DMC	6
J7	VDD_DMC	6
K7	VDD_DMC	6
A1	GND	6
A20	GND	6
B1	GND	6
B2	GND	6
B19	GND	6
C3	GND	6
C4	GND	6
C5	GND	6
C6	GND	6
C14	GND	6
C15	GND	6
C16	GND	6
C17	GND	6
C18	GND	6

Sym

F

2

2

2

2

2

2

2

2

3

3

3

3

3

3

3

3

3

4

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
D2	GND	6
D4	GND	6
D5	GND	6
D6	GND	6
D7	GND	6
D12	GND	6
D13	GND	6
D14	GND	6
D15	GND	6
D8	VDD_EXT	7
D9	VDD_EXT	7
D10	VDD_EXT	7
D11	VDD_EXT	7
K4	VDD_EXT	7
L4	VDD_EXT	7
M4	VDD_EXT	7
M16	VDD_EXT	7
N4	VDD_EXT	7

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
N16	VDD_EXT	7
P4	VDD_EXT	7
P16	VDD_EXT	7
R4	VDD_EXT	7
R16	VDD_EXT	7
T5	VDD_EXT	7
T16	VDD_EXT	7
U6	VDD_EXT	7
U7	VDD_EXT	7
U8	VDD_EXT	7
U9	VDD_EXT	7
U10	VDD_EXT	7
U11	VDD_EXT	7
U12	VDD_EXT	7
U13	VDD_EXT	7
U14	VDD_EXT	7
U15	VDD_EXT	7
D16	GND	7

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
D17	GND	7
D18	GND	7
E3	GND	7
E18	GND	7
F3	GND	7
F18	GND	7
G3	GND	7
G18	GND	7
H2	GND	7
H3	GND	7
H8	GND	7
H9	GND	7
H10	GND	7
H11	GND	7
H12	GND	7
H13	GND	7
H18	GND	7
J3	GND	7

Sym

F

2

2

3

3

3

3

3

3

3

3

3

3

4

4

4

4

4

4

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
J8	GND	7
J9	GND	7
J10	GND	7
J11	GND	7
J12	GND	7
J13	GND	7
J18	GND	7
E4	VDD_INT	8
E5	VDD_INT	8
E6	VDD_INT	8
E7	VDD_INT	8
E8	VDD_INT	8
E9	VDD_INT	8
E10	VDD_INT	8
E11	VDD_INT	8
E12	VDD_INT	8
E13	VDD_INT	8
E14	VDD_INT	8

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
E15	VDD_INT	8
E16	VDD_INT	8
E17	VDD_INT	8
F4	VDD_INT	8
F5	VDD_INT	8
F16	VDD_INT	8
F17	VDD_INT	8
G4	VDD_INT	8
G5	VDD_INT	8
G16	VDD_INT	8
G17	VDD_INT	8
H4	VDD_INT	8
H5	VDD_INT	8
H16	VDD_INT	8
H17	VDD_INT	8
J5	VDD_INT	8
J14	VDD_INT	8
J15	VDD_INT	8

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
J16	VDD_INT	8
J17	VDD_INT	8
K5	VDD_INT	8
K6	VDD_INT	8
K14	VDD_INT	8
K15	VDD_INT	8
K16	VDD_INT	8
L5	VDD_INT	8
L6	VDD_INT	8
L7	VDD_INT	8
L14	VDD_INT	8
L15	VDD_INT	8
M5	VDD_INT	8
M6	VDD_INT	8
M7	VDD_INT	8
M14	VDD_INT	8
N6	VDD_INT	8
N7	VDD_INT	8

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
N14	VDD_INT	8
P6	VDD_INT	8
P7	VDD_INT	8
P8	VDD_INT	8
P9	VDD_INT	8
P10	VDD_INT	8
P11	VDD_INT	8
P12	VDD_INT	8
P13	VDD_INT	8
P14	VDD_INT	8
R6	VDD_INT	8
R7	VDD_INT	8
R8	VDD_INT	8
R9	VDD_INT	8
R10	VDD_INT	8
R11	VDD_INT	8
R12	VDD_INT	8
R13	VDD_INT	8

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
R14	VDD_INT	8
K1	GND	8
K2	GND	8
K3	GND	8
K8	GND	8
K9	GND	8
K10	GND	8
K11	GND	8
K12	GND	8
K13	GND	8
K17	GND	8
K18	GND	8
K19	GND	8
K20	GND	8
L2	GND	8
L3	GND	8
L8	GND	8
L9	GND	8

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
L10	GND	8
L11	GND	8
L12	GND	8
L13	GND	8
L16	GND	8
L17	GND	8
M1	GND	8
M2	GND	8
M8	GND	8
M9	GND	8
M10	GND	8
M11	GND	8
M12	GND	8
M13	GND	8
M17	GND	8
M18	GND	8
N2	GND	8
N8	GND	8

Sym

F

8

8

8

8

8

8

9

9

9

9

9

9

9

9

9

9

1

1

Component Definition for: "ADSP-21569WCBCZ8"

Pin Data:

Pin Number	Pin Name	Gate Number
N9	GND	8
N10	GND	8
N11	GND	8
N12	GND	8
N13	GND	8
N17	GND	8
N18	GND	8
P1	GND	8
P17	GND	8
P19	GND	8
P20	GND	8
R2	GND	8
R17	GND	8
T1	GND	8
T4	GND	8
T17	GND	8
U1	GND	8
U4	GND	8

Sym

F

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

1

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
U5	GND	8
U16	GND	8
U17	GND	8
V3	GND	8
V4	GND	8
V15	GND	8
V16	GND	8
V18	GND	8
W1	GND	8
W2	GND	8
W19	GND	8
W20	GND	8
Y1	GND	8
G10	VDD_REF	9
G11	VDD_REF	9
M15	VDD_REF	9
N5	VDD_REF	9
N15	VDD_REF	9

Syn

F

1

1

1

1

1

1

1

1

1

1

1

1

1

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
P5	VDD_REF	9
P15	VDD_REF	9
R5	VDD_REF	9
R15	VDD_REF	9
T6	VDD_REF	9
T7	VDD_REF	9
T8	VDD_REF	9
T9	VDD_REF	9
T10	VDD_REF	9
T11	VDD_REF	9
T12	VDD_REF	9
T13	VDD_REF	9
T14	VDD_REF	9
T15	VDD_REF	9
Y2	GND	9
Y5	GND	9
Y7	GND	9
Y13	GND	9

Component Definition for: "ADSP-21569WCBCZ8"		
Pin Data:		
Pin Number	Pin Name	Gate Number
Y16	GND	9
Y19	GND	9
Y20	GND	9

Pin Mapping:	
Pad Number	Component Pin Reference
388	Y8
349	V9
369	W9
389	Y9
370	W10
350	V10
390	Y10
371	W11
351	V11
391	Y11
392	Y12
372	W12
373	W13
352	V12
378	W18
357	V17

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
360	V20
359	V19
338	U18
318	T18
299	R19
339	U19
319	T19
340	U20
320	T20
298	R18
278	P18
300	R20
79	D19
80	D20
60	C20
59	C19
19	A19
40	B20
38	B18
18	A18
16	A16
36	B16
15	A15
35	B15

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
34	B14
14	A14
13	A13
33	B13
37	B17
17	A17
99	E19
5	A5
25	B5
26	B6
23	B3
2	A2
3	A3
63	D3
42	C2
61	D1
82	E2
81	E1
121	G1
141	H1
122	G2
161	J1
162	J2
102	F2

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
101	F1
140	G20
164	J4
24	B4
4	A4
139	G19
12	A12
6	A6
32	B12
119	F19
159	H19
41	C1
120	F20
160	H20
179	J19
180	J20
100	E20
243	N3
263	P3
262	P2
283	R3
281	R1
302	T2
303	T3

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
341	V1
323	U3
342	V2
322	U2
348	V8
366	W6
386	Y6
367	W7
368	W8
374	W14
394	Y14
365	W5
347	V7
384	Y4
383	Y3
346	V6
363	W3
364	W4
345	V5
48	C8
27	B7
47	C7
28	B8
49	C9

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
7	A7
31	B11
53	C13
52	C12
10	A10
30	B10
29	B9
8	A8
241	N1
11	A11
9	A9
50	C10
259	N19
260	N20
239	M19
240	M20
218	L18
220	L20
398	Y18
377	W17
354	V14
397	Y17
376	W16
395	Y15

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
375	W15
353	V13
201	L1
223	M3
51	C11
219	L19
106	F6
107	F7
108	F8
109	F9
110	F10
111	F11
112	F12
113	F13
114	F14
115	F15
126	G6
127	G7
128	G8
129	G9
132	G12
133	G13
134	G14
135	G15

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
146	H6
147	H7
154	H14
155	H15
166	J6
167	J7
187	K7
1	A1
20	A20
21	B1
22	B2
39	B19
43	C3
44	C4
45	C5
46	C6
54	C14
55	C15
56	C16
57	C17
58	C18
62	D2
64	D4
65	D5

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
66	D6
67	D7
72	D12
73	D13
74	D14
75	D15
68	D8
69	D9
70	D10
71	D11
184	K4
204	L4
224	M4
236	M16
244	N4
256	N16
264	P4
276	P16
284	R4
296	R16
305	T5
316	T16
326	U6
327	U7

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
328	U8
329	U9
330	U10
331	U11
332	U12
333	U13
334	U14
335	U15
76	D16
77	D17
78	D18
83	E3
98	E18
103	F3
118	F18
123	G3
138	G18
142	H2
143	H3
148	H8
149	H9
150	H10
151	H11
152	H12

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
153	H13
158	H18
163	J3
168	J8
169	J9
170	J10
171	J11
172	J12
173	J13
178	J18
84	E4
85	E5
86	E6
87	E7
88	E8
89	E9
90	E10
91	E11
92	E12
93	E13
94	E14
95	E15
96	E16
97	E17

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
104	F4
105	F5
116	F16
117	F17
124	G4
125	G5
136	G16
137	G17
144	H4
145	H5
156	H16
157	H17
165	J5
174	J14
175	J15
176	J16
177	J17
185	K5
186	K6
194	K14
195	K15
196	K16
205	L5
206	L6

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
207	L7
214	L14
215	L15
225	M5
226	M6
227	M7
234	M14
246	N6
247	N7
254	N14
266	P6
267	P7
268	P8
269	P9
270	P10
271	P11
272	P12
273	P13
274	P14
286	R6
287	R7
288	R8
289	R9
290	R10

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
291	R11
292	R12
293	R13
294	R14
181	K1
182	K2
183	K3
188	K8
189	K9
190	K10
191	K11
192	K12
193	K13
197	K17
198	K18
199	K19
200	K20
202	L2
203	L3
208	L8
209	L9
210	L10
211	L11
212	L12

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
213	L13
216	L16
217	L17
221	M1
222	M2
228	M8
229	M9
230	M10
231	M11
232	M12
233	M13
237	M17
238	M18
242	N2
248	N8
249	N9
250	N10
251	N11
252	N12
253	N13
257	N17
258	N18
261	P1
277	P17


Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
279	P19
280	P20
282	R2
297	R17
301	T1
304	T4
317	T17
321	U1
324	U4
325	U5
336	U16
337	U17
343	V3
344	V4
355	V15
356	V16
358	V18
361	W1
362	W2
379	W19
380	W20
381	Y1
130	G10
131	G11

Component Definition for: "ADSP-21569WCBCZ8"	
Pin Mapping:	
Pad Number	Component Pin Reference
235	M15
245	N5
255	N15
265	P5
275	P15
285	R5
295	R15
306	T6
307	T7
308	T8
309	T9
310	T10
311	T11
312	T12
313	T13
314	T14
315	T15
382	Y2
385	Y5
387	Y7
393	Y13
396	Y16
399	Y19
400	Y20

Symbol Name: ADSP-21569WCBCZ8_A

RefDes
Type


1 of 12



Symbol Name: ADSP-21569WCBCZ8_B

RefDes
Type


2 of 12



Symbol Name: ADSP-21569WCBCZ8_C

RefDes
Type


3 of 12



Symbol Name: ADSP-21569WCBCZ8_D

RefDes
Type


4 of 12



Symbol Name: ADSP-21569WCBCZ8

RefDes
Type

5 of 12



Symbol Name: ADSP-21569WCBCZ8_04

RefDes
Type


10 of 12



Symbol Name: ADSP-21569WCBCZ8_05

RefDes
Type


11 of 12




Symbol Name: ADSP-21569WCBCZ8_06

RefDes
Type


12 of 12




Symbol Name: ADSP-21569WCBCZ8_00




Symbol Name: ADSP-21569WCBCZ8_01




Symbol Name: ADSP-21569WCBCZ8_02




Symbol Name: ADSP-21569WCBCZ8_03



9 of 12





Default Padstyle: c36

Template Variables :

Height = 54.33071

MINHEIGHT = 11.81102

RefDes = RefDes

Type = DEV

PN = PN

DEV = DEV

VAL = VAL

TOL = TOL

RefDes2 = RefDes2

TEMPLATE = ADI_bga_c.adt

NAME = BC_400_3

CP = 31.49606

RP = 31.49606

C = 20

CRN = UL

PF = A1

L = ABCDEFGHJKLMNPRTUVWY

PO = A1

PC = 400

R = 20

S = A1A2

Template Variables :

CHK = o400

AdiDefGridDocStyle = 1

CHGT = 54.33071

CMHGT = 11.81102

PSH = Round

SMOS = 0

SPOS = 0

NOT = 1

BODY_W = 669.2913

BODY_H = 669.2913

BODYOFFX = 0

BODYOFFY = 0

KO = 0

KOW = 160

KOH = 210

HTT = 0

CMARK = 0

HTSMOS = 0

HTW = 150

HTH = 200

A1_PSH = Oblong

Template Variables :

A1_SMOS = 0

A1_SPOS = 0

A1_PADW = 60

A1_PADH = 90

A1_DRL = 30

A2_PSH = Oblong

A2_SMOS = 0

A2_SPOS = 0

A2_PADW = 90

A2_PADH = 60

A2_DRL = 30

FID = 0

PROT = 0

REVLEVEL = A0

3D = 1

MATP = Aluminum

MATB = Black

OX2 = 0

OY = 0

OZ = 0

OriginalPinCount = 400

