

Item	Qty	Ref	Desc	Manufacturer / Part #
1	24	C1-C12,C16,C20-C24,C26, C27,C30-C33,C35,C39	CAP, X5R 0.1uF 10V 10% 0402	AVX 0402ZD104KAT
2	4	C3,C34,C36,C37	CAP, X5R 4.7uF 6.3V 20% 0603	TDK C1608X5R0J475MT
3	1	C7	CAP, COG 8pF 50V +/-0.5pF 0402	TDK C1005COG1H080D
4	2	C18,C17	CAP, X5R 1uF 10V 10% 0603	TDK C1608X5R1A105K
5	2	C19,C29	CAP, X5R 2.2uF 6.3V 10% 0603	TAIYO YUDEN JMK107BJ225KAT
6	1	C25	CAP, NPO 33pF 50V 5% 0402	AVX 04025A330JAT
7	4	E1,E3,E4,E5	TURRETS	MILLMAX 2501-2
8	2	JP3,JP1	HEADER,3PIN, 2mm	COMM CON 2802S-03G2
9	8	JP4,JP7,JP13,JP14,JP19-JP22	HEADER,2PIN, 2mm	COMM CON 2802S-02G2
10	2	J6,J9	CONN, BNC, SMA 50-OHM EDGE-LANCH	E.F.JOHNSON, 142-0701-851
11	1	L1	FERRITE BEAD, 0603	MURATA BLM18BB470SN1
12	16	R1,R7,R8,R13-R21,R23-R26	RES, 100 OHMS 5% 1/16W 0402	AAC CR05-101JM
13	3	R2,R3,R4	RES, 4.99K OHMS 1% 1/16W 0603	AAC CR16-4991FM
14	1	R5	RES, 2K OHMS 5% 1/16W 0402	AAC CR05-202JM
15	1	R6	RES, 4.7K OHMS 5% 1/16W 0402	AAC CR05-472JM
16	2	R11,R12	RES, 12.5 OHMS 1% 1/16W 0402	AAC CR05-12R5FM
17	2	R9,R10	RES, 24.9 OHMS 1% 1/16W 0402	AAC CR05-24R9FM
18	4	R27,R28,R29,R30	RES, 1K OHMS 5% 1/16W 0402	AAC CR05-102JM
19	1	T1	XFMR,	MACOM ETC1-1-13
20	1	T2	XFMR,	MACOM ETC1-1T
21	2	U2,U1	IC, FIN1108T	FAIRCHILD FIN1108MTDX
22	1	U3	IC, LTC2221CUP	LINEAR TECH. LTC2221CUP
23	1	U4	IC, 24LC025	MICROCHIP TECH. 24LC025
24	9	JP1,JP3,JP7,JP13,JP14,JP19-JP22	SHUNT	COMM CON CCIJ2MM-138G
25	4		STANDOFF, SNAP ON	KEYSTONE_8831