



NOTES:

1. DIMENSIONS ARE IN MILLIMETERS.
2. MARKING IS FOR PACKAGE ORIENTATION REFERENCE ONLY. PACKAGE USES 2 CHARACTER PRODUCT CODE.
3. LEAD CENTERLINES TO BE AT TRUE POSITION AS DEFINED BY BASIC DIMENSION "e",  $\pm 0.05$ .
4. CALENDAR YEAR BINARY DATE CODE (REFER TO PG. 2 TABLE 1 FOR TRANSLATION).
5. 6 WEEKLY DATE BINARY CODE (REFER TO PG. 2 TABLE 2 FOR TRANSLATION).
6. MATERIAL MUST BE COMPLIANT WITH MAXIM SPECIFICATION 10-0131 FOR SUBSTANCE CONTENT, MUST BE EU ROHS COMPLIANT WITHOUT EXEMPTION AND Pb-FREE.
7. MEETS JEDEC MO-252 VARIATION WAAD.
8. LEAD PLATING MATERIAL: GOLD, 0.5 MICROMETER MINIMUM THICKNESS.
9. ALL DIMENSIONS APPLY TO BOTH LEADED (-) & PbFREE (+) PKG. CODES.

SYMBOL	COMMON DIMENSIONS		
	MIN.	NOM.	MAX.
A	0.65	0.72	0.80
A1	--	0.20	--
A2	0.00	--	0.05
D	1.45	1.50	1.55
E	0.95	1.00	1.05
L	0.30	0.35	0.40
L1	0.00	--	0.08
L2	0.05	--	0.10
b	0.17	0.20	0.23
e	0.50 BSC.		
Pkg. Code	L611-1, L611-1C L611-2, L611-2C		



TITLE:  
PACKAGE OUTLINE,  
6L uDFN, 1.5x1.0x0.75mm

APPROVAL  
RDHINI KESAVAN

DOCUMENT CONTROL NO.  
21-0147

REV. M 1/2

-DRAWING NOT TO SCALE-

**TABLE 1** Translation Table for Calendar Year

Code Calendar Year	2016	2017	2018	2019	2020	2021	2022	2023	2024	2025	2026	2027	2028	2029	2030
	■	■	□	■	□	□	□	■	□	□	■	□	■	■	■
	□	■	■	■	□	□	■	□	□	■	□	■	□	■	■
	■	□	■	■	□	■	□	□	■	□	□	■	■	□	■
	■	■	■	■	■	□	□	□	■	■	■	□	□	□	□

Legend: ■ Marked with bar      □ Blank space - no bar required

**TABLE 2** Translation Table for Payweek Binary

Code Payweek	06-11	12-17	18-23	24-29	30-35	36-41	42-47	48-51	52, 53-05
	□	□	□	■	□	□	■	□	■
	□	□	■	□	□	■	□	■	□
	□	■	□	□	■	□	□	■	■
	■	□	□	□	■	■	■	□	□

Legend: ■ Marked with bar      □ Blank space - no bar required



TITLE:  
PACKAGE OUTLINE,  
6L uDFN, 1.5x1.0x0.75mm

APPROVAL  
RDHINI KESAVAN

DOCUMENT CONTROL NO.  
21-0147

REV.  
M

2/2