

Component Definition for: "ADP2303ARDZ"


Number of Pins: 9	Number of Gates: 1
Name of Pattern: RD_8_1	Number of pattern Pins: 9
Symbol gating Information:	
Symbol name for gate 1 is ADP2303ARDZ	



Pin Data:						
Pin Number	Pin Name	Gate Number	Symbol Pin	Gate Equiv.	Pin Equiv.	Pin Type
1	BST	1	2	0	0	11
2	VIN	1	1	0	0	11
3	EN	1	5	0	0	11
4	PGOOD	1	3	0	0	11
5	FB	1	4	0	0	11
6	NC	1	9	0	0	11
7	GND	1	7	0	0	11
8	SE	1	6	0	0	11
9	EPAD	1	8	0	0	11

Pin Mapping:	
Pad Number	Component Pin Reference
1	1
2	2
3	3
4	4
5	5
6	6
7	7
8	8
9	9

Symbol Name: ADP2303ARDZ

RefDes
Type





Default Padstyle: r198_56
Pin One Padstyle: r198_56
Heat Tab Padstyle: r229_229

Alt 1 Padstyle: b152_229h76
Alt 2 Padstyle: b229_152h76

--

Height = 68.89764
MINHEIGHT = 1.968504
RefDes = RefDes
Type = DEV
PN = PN
DEV = DEV
VAL = VAL
TOL = TOL
RefDes2 = RefDes2
OZ = 0
OriginalPinCount = 9
TEMPLATE = ADI_SO_C.adt
NAME = RD_8_1
N = 8
PSH = Rectangle
SMOS = 0
SPOS = 0
BODY_W = 153.5433
LX = 244.0945
LMX = 244.0945
RP = 50
BODY_H = 192.9134
FOOT_L = 50
FOOT_W = 20.07874
CHGT = 68.89764
CMHGT = 1.968504
NT = Arc

TT = Normal Material

UTOE = 0

UHEEL = 0

USIDE = 0

UCE = 0

--

KO = 0
KOW = 78.74
KOH = 78.74
HTT = 1
HTSMOS = 0
HTSPOS = 0
HTW = 90.15748
HTH = 90.15748
HTXO = 0
HTYO = 0
WVS = 0
WV = 0
PPPSH = Round
HTPADS = 60
HTDRL = 35
A1_PSH = Oblong
A1_SMOS = 0
A1_SPOS = 0
A1_PADW = 60
A1_PADH = 90
A1_DRL = 30
A2_PSH = Oblong
A2_SMOS = 0
A2_SPOS = 0
A2_PADW = 90
A2_PADH = 60
A2_DRL = 30

MWA = 4

RSMB = 2

ISML = 0

PROT = 0

REVLEVEL = A0

--

3D = 1
LEAD_T = 10
MATP = Aluminum
MATB = Gray
OX2 = 0
OY = 0

