




REVISION HISTORY			
ECO	REV	DESCRIPTION	APPR DATE
	4	PRODUCTION	TIM K. 06/28/16



NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600.
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE 0.062 +/- .005
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON ALL THE LAYERS
-FLAMMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: -DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
-ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
-HOLE LOCATION TOLERANCES ARE +/-0.003 IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
-FOR SILKSCREENS: USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES		APPROVALS		LINEAR TECHNOLOGY		1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 WWW.LINEAR.COM LTC CONFIDENTIAL FOR CUSTOMER USE ONLY	
TOLERANCES:		PCB DES.	HZ				
0.XX = ± 0.01 0.XXX = ± 0.005		APP ENG.	TIM K.	TITLE: FABRICATION DRAWING			
INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION				15VIN, +/- 5A MONOLITHIC BUCK REGULATOR			
				SIZE	IC NO.	REV	
				N/A	DRG NO.	4	
		SCALE = NONE		LTC3623EUDD		DEMO CIRCUIT 2131A	
				FILENAME: 2131A-4.PCB		SHT 1 OF 1	



1630 MCCARTHY BLVD
MILFORD, MA 01803
(978) 683-8000
WWW.LINEAR.COM
LTC CONFIDENTIAL -
FOR CUSTOMER USE ONLY

SIZE	QTY	SYM	PLATED	TOL
0.187	4	+	YES	+/-0.003
0.01	276	X	YES	+/-0.003
0.095	7	□	YES	+/-0.003
0.006	8	◇	YES	+/-0.003
0.035	21	⊗	YES	+/-0.003