



TOP SILKSCREEN  
 LINEAR TECHNOLOGY DATE: 01-29-2016  
 DC2460A-2 \* LTC5566  
 DUAL PROGRAMMABLE GAIN MIXER




REVISION HISTORY			
ECO	REV	DESCRIPTION	APP. ENG.
-	2	2nd PROTO	WESTON S.

## NOTES: UNLESS OTHERWISE SPECIFIED

1. WORKMANSHIP SHALL BE IN ACCORDANCE WITH IPC-A-610.
2. ASSEMBLY PROCESS SHALL INCLUDE: REFLOW SOLDER TOP SIDE SMD. MAXIMUM SOLDER TEMPERATURE IS 240 DEGREES CELSIUS.
3. PARTS TO OMIT WILL BE SPECIFIED ON THE BILL OF MATERIALS. LOCATIONS OF OMITTED PARTS SHALL BE FREE OF SOLDER. MASK THE SOLDER STENCIL WHERE SMT PARTS ARE OMITTED.
4. NO SHUNT
5. DEPANELIZE BOARDS AFTER ASSEMBLY AND ROUTE-OUT THE BREAKOUT TABS ON FOUR SIDES OF THE BOARD EDGE.
6. DO NOT APPLY ANY KIND OF ASSEMBLY STAMP OR QA STAMP TO ANY BOARD.
7. INSTALL J1-J4 CONNECTORS AS SHOWN BELOW:



APPROVALS		 1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 www.linear.com LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
PCB DES.	SM		
APP ENG.	WESTOM S.	TITLE: TOP ASSEMBLY DRAWING	
		DUAL PROGRAMMABLE GAIN MIXER	
		SIZE	IC NO.
		N/A	LTC5566
			DEMO CIRCUIT 2460A
			REV.
			2
SCALE = NONE		FILENAME: DC2460A-2.PCB	
		SHT 1 OF 2	