

File E214100
Project 4787281617

June 4, 2016

REPORT

on

COMPONENT - Nonoptical Isolating Devices

ANALOG DEVICE INC.
WILMINGTON, MA

Copyright © 2016 UL LLC

UL LLC authorizes the above named company to reproduce this Report only for purposes as described in the Conclusion. The Report should be reproduced in its entirety; however to protect confidential product information, the Construction Details Descriptive pages may be excluded.

DESCRIPTION

PRODUCT COVERED:

USR - Single Protection Non-Optical Isolator, Models ADuM110NzRZ, ADUM13xyzBRWZ, ADUM13xyzBRZ, ADUM14xyzBRWZ, ADUM14xyzBRZ, ADUM210NzBRIZ, ADUM23xyzBRWZ, ADUM24xyzBRWZ, ADUM4135BRWZ, where x, y, and z represent any alphanumeric character. All models may have additional suffixes.

MAXIMUM RATINGS PER SIDE (at 25°C ambient) (\$):

Model	Current (mA)		Power (mW)		Isolation Voltage at 60 sec (Vrms)	Max Operating Ambient Temp (°C)	Max Junction Temp (°C)	Max Storage Temp (°C)	Max Data Rate, Mbps
	Encoder (Side 1)	Decoder (Side 2)	Encoder (Side 1)	Decoder (Side 2)					
ADuM110NzRZ	3.6	4.9	18	24.5	3000	125	150	150	150
ADUM13xyzBRZ	9.4	8	47	40	3000	125	150	150	150
ADUM14xyzBRZ	11.8	10.3	59	51.5	3000	125	150	150	150
ADUM13xyzBRWZ	9.4	8	47	40	3000	125	150	150	150
ADUM14xyzBRWZ	11.8	10.3	59	51.5	3000	125	150	150	150
ADUM23xyzBRWZ	9.4	8	47	40	5000	125	150	150	150
ADUM24xyzBRWZ	11.8	10.3	59	51.5	5000	125	150	150	150
ADUM210NzBRIZ	3.6	4.9	18	24.5	5000	125	150	150	150
ADUM4135BRWZ	4.78	4.82	28.7	144	5000	125	150	150	150

(\$) - For ambient temperatures higher than 25°C and up to T_{moa}, refer to manufacturer's specifications and/or thermal derating curve data for complete electrical ratings.

GENERAL:

These non-optical isolator devices consist of a transmitter coupled to a receiver. The transmitter and receiver are separated by an insulating barrier. Internal chips are connected to lead frames that are molded into the enclosure.

TECHNICAL CONSIDERATIONS (NOT FOR FIELD REPRESENTATIVE'S USE):

Use - For use only in products where the acceptability of the combination is determined by UL LLC.

USR indicates this product was investigated under the UL Standard for Safety for Optical Isolators, UL 1577, Fifth Edition.

CNR indicates this product was investigated under the Canadian Certification Notice, CSA Component Acceptance Service No. 5A.

Conditions of Acceptability - Each device shall be reviewed with respect to the following conditions of acceptability:

1. The capability of the device to control a load has not been investigated.
2. These devices should be installed in a suitable end product enclosure.
3. The maximum junction temperature shall not be exceeded.
4. For single protection devices, the insulation to the case has not been evaluated. For double protection devices, the insulation to the case has been evaluated to the isolation voltage specified in the ratings table.
5. In addition to meeting single protection requirements, double protection optical isolators have also been investigated for use in up to 250 V, 50/60 Hz circuits in audio, video, and similar equipment in applications in which breakdown of the optical isolator may result in a risk of fire, electrical shock, or injury to persons.

CONSTRUCTION DETAILS:

General - The product shall be constructed in accordance with the following description. All dimensions are approximate, unless specified as "max" or "min".

Markings - As specified in the Section General.

MODEL ADUM4135BRWZ

General - Model ADUM4135BRWZ represents all models.

1. Encoder - FET input.
2. Decoder - FET output.
3. Isolation Chip - As described below.

Optical Isolator Model	Isolation Chip Model
ADUM14xyzBRWZ, ADUM13xyzBRWZ ADUM24xyzBRWZ, ADUM23xyzBRWZ	ADUM14XTC
ADUM210NzBRIZ	ADUM12XTC
ADUM4135BRWZ	ADUM413XTC
ADuM110NzRZ	ADUM12XTC
ADUM13xyzBRZ, ADUM14xyzBRZ	ADUM14XTC

4. Lead Frame and Bond Wire - Metal employed for current carrying parts shall be of stainless steel, plated steel, silver, gold, copper, nickel, aluminum, an alloy of the same, or an equivalent material.
5. Casing (Outer Mold) - Epoxy type, Sumitomo Bakelite, Type G700LY.
6. Insulation Transformer Compound Coupling - Polyimide film, Asahi Kasei Corporation, Type I-8124ER, 0.025 mm minimum thick.