



产品认证证书

证书编号: CQC16001147385

发证日期: 2021 年 12 月 23 日

有效期至: 长期有效

委托人名称 亚德诺投资有限公司
及注册地址 上海市黄浦区湖滨路 222 号 11 层 (实际楼层为 10 层) 1107 室

制造商名称 Analog Devices
及注册地址 804 Woburn StreetWilmingtonMA 美国

生产企业名称 Analog Devices Gen. Trias
及生产地址 Gateway Business Park,Javalera, Gen. Trias,Cavite, 菲律宾

产品名称和系列、规格、型号 数字隔离器
见附件

产品标准和技术要求 GB 4943.1-2011

认证模式 产品型式试验+初次工厂检查+获证后监督

上述产品符合 CQC11-471543-2015 认证规则的要求, 特发此证。

本证书为变更证书, 证书首次颁发日期: 2016 年 06 月 27 日

本证书的有效性依据发证机构的定期监督获得保持。

可通过扫描下方二维码或登录国家认监委网站 (www.cnca.gov.cn) 查验证书信息



签发:

谢肇煦



中国质量认证中心



产品认证证书

证书编号: CQC16001147385

第 1 页 共 1 页

本证书及附件应同时使用, 信息查验说明见证书页

纸号:

ADuM140D0BRWZ, ADuM140D1BRWZ, ADuM140E0BRWZ, ADuM140E1BRWZ, ADuM141D0BRWZ, ADuM141D1BRWZ, ADuM141E0BRWZ, ADuM141E1BRWZ, ADuM142D0BRWZ, ADuM142D1BRWZ, ADuM142E0BRWZ, ADuM142E1BRWZ, ADuM130D0BRWZ, ADuM130D1BRWZ, ADuM130E0BRWZ, ADuM130E1BRWZ, ADuM131D0BRWZ, ADuM131D1BRWZ, ADuM131E0BRWZ, ADuM131E1BRWZ, ADuM132D0BRWZ, ADuM132D1BRWZ, ADuM132E0BRWZ, ADuM132E1BRWZ, ADuM240D1BRWZ, ADuM240D0BRWZ, ADuM240E1BRWZ, ADuM240E0BRWZ, ADuM241D1BRWZ, ADuM241D0BRWZ, ADuM241E1BRWZ, ADuM241E0BRWZ, ADuM242D1BRWZ, ADuM242D0BRWZ, ADuM242E1BRWZ, ADuM242E0BRWZ, ADuM230D1BRWZ, ADuM230D0BRWZ, ADuM230E1BRWZ, ADuM230E0BRWZ, ADuM231D1BRWZ, ADuM231D0BRWZ, ADuM231E1BRWZ, ADuM231E0BRWZ, ADuM140D0WBRWZ, ADuM140D1WBRWZ, ADuM140E0WBRWZ, ADuM140E1WBRWZ, ADuM141D0WBRWZ, ADuM141D1WBRWZ, ADuM141E0WBRWZ, ADuM141E1WBRWZ, ADuM142D0WBRWZ, ADuM142D1WBRWZ, ADuM142E0WBRWZ, ADuM142E1WBRWZ, ADuM130D0WBRWZ, ADuM130D1WBRWZ, ADuM130E0WBRWZ, ADuM130E1WBRWZ, ADuM131D0WBRWZ, ADuM131D1WBRWZ, ADuM131E0WBRWZ, ADuM131E1WBRWZ, ADuM132D0WBRWZ, ADuM132D1WBRWZ, ADuM132E0WBRWZ, ADuM132E1WBRWZ, ADuM240D1WBRWZ, ADuM240D0WBRWZ, ADuM240E1WBRWZ, ADuM240E0WBRWZ, ADuM241D1WBRWZ, ADuM241D0WBRWZ, ADuM241E1WBRWZ, ADuM241E0WBRWZ, ADuM242D1WBRWZ, ADuM242D0WBRWZ, ADuM242E1WBRWZ, ADuM242E0WBRWZ, ADuM230D1WBRWZ, ADuM230D0WBRWZ, ADuM230E1WBRWZ, ADuM230E0WBRWZ, ADuM231D1WBRWZ, ADuM231D0WBRWZ, ADuM231E1WBRWZ, ADuM231E0WBRWZ, AD71255BRWZ, AD71256BRWZ, AD71257BRWZ
外部爬电距离: 7.7mm, 通过热循环测试, 基本绝缘或附加绝缘: 最大工作电压: 760V 有效值, 1075V 峰值。加强绝缘: 最大工作电压: 380V 有效值, 537V 峰值



中国质量认证中心