





ECO	REV	DESCRIPTION	APPROVAL	DATE
	2	PRODUCTION	LEO C.	08/01/10

NOTES: UNLESS OTHERWISE SPECIFIED,

1. FAB PER IPC-A-600
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE 1.6 +/- 0.127
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, 0.0254 THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-0.0762 IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPI BOTH SIDES, COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
-SILKSCREEN BOTH SIDES WITH WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCB SHALL BE RoHS COMPLIANT.
8. SCORING:



SIZE	QTY	SYM	PLATED	TOL
0.25	55	+	YES	+/-0.08
0.9	20	×	YES	+/-0.08
1.6	4	□	YES	+/-0.13
1.8	2	⊗	NO	+/-0.13

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS TOLERANCES ON ANGLE ±1° XX ± 0.254 XXX ± 0.127 INTERPRET DIM AND TOL PER ASME Y14.5M-1994 THIRD ANGLE PROJECTION 	APPROVALS				1630 MCARTHUR BLVD MILPITAS, CA 95035 PH: (408)432-1900 www.linear.com LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
	PCB DES.	MI			TITLE: FABRICATION DRAWING, 16-BIT DELTA SIGMA SPI ADC	
	APP. ENG.	LEO C.				
			SIZE N/A	IC NO LTC2470CDD DEMO CIRCUIT 1628A	REV 2	
DO NOT SCALE DRAWING	SCALE: NONE		FILENAME: 1628a-2.PCB		SHT 1 of 1	