


REVISIONS			
REV	DATE	APPR	DATE




L1-COMPONENT SIDE

- LAYER 1 (COMPONENT SIDE)
- LAYER 2 (GND)
- LAYER 3 (GND)
- LAYER 4 (SOLDER SIDE)


NOTES : Unless Otherwise Specified
PCB's SHOULD BE RoHS COMPLIANT.

- 1. MATERIAL : FR4 OR EQUIVALENT EPOXY
2 OZ OUTER, 1 OZ INNER COPPER CLAD
- THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS
- 2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
- GOLD IMMERSION BOTH SIDES.
- 3. SOLDER MASK : BOTH SIDES USING GREEN LPI OR EQUIVALENT
- 4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
- 5. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE,
BUT PAD SIZE MAY BE MODIFIED TO MEET END FINISH.

6. SCORING



Fabrication Drawing

APPROVALS				1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE			
CHECK	Antonio K				
DESIGN					
ENGR	Mitchell Lee				
			TITLE: LT4356CDE OVERVOLTAGE PROTECTION REGULATOR		
			SIZE	Demo Circuit 1018B	REV. B
			NONE		
SCALE = NONE			DESIGN #	DC1018A.DSN SHT 1 of 1	

SIZE	QTY	SYM	PLTD	TOL
12	219	+	YES	+/-0.003
187	4	X	NO	+/-0.003
70	2	□	NO	+/-0.003
205	4	◇	YES	+/-0.003
94	4	⊗	YES	+/-0.003
63	5	⊗	YES	+/-0.003
40	2	†	YES	+/-0.003