



REVISIONS			
REV	DESCRIPTION	APPR	DATE



NOTES : Unless Otherwise Specified


1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISHED ON OUTER LAYERS.
1 OZ. COPPER FINISHED ON INNER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003
INCH IN RELATION TO CENTER
5. SOLDER MASK : SMOBC USING LPI BOTH SIDES COLOR GREEN.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



FAB DRAWING

SIZE	QTY	SYM	PLTD
95	11	+	PLTD
10	61	x	PLTD
70	2	◇	NPLTD

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ±1
2 PLACE ±.01 3 PLACE ±.005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS					1630 McCarthy Blvd. Milpitas, CA 95035 Ph: (408)432-1900	
	INIT	DATE				
DRAWN	JUNE WU	7/24/03				
CHECK						
DESIGN						
ENGR	Dongyan Z.	7/24/03				
			TITLE: LT1943EFE, High Current Quad Outout			
			Switching Regulator For 5V Input TFT-LCD Panels			
			SIZE	A	DEMO	REV. A
					DC697A	
SCALE = NONE			DES-230639		SHT 1 of 1	