


REVISIONS


REV	APPR	DATE
-----	------	------

NOTES: UNLESS OTHERWISE SPECIFIED:

- ARTWORK P/N DC741A Rev3. 4-LAYERS.
- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4
.062 +/- .005 INCH THICKNESS WITH 2 OZ.
COPPER FINISH ON TWO OUTER LAYERS AND
1 OZ. COPPER ON TWO INTERNAL LAYERS.
FLAMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER
MASK OVER BARE COPPER, COLOR, GREEN LPI.
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
SILKSCREEN COMPONENT SIDE WITH WHITE NON-
CONDUCTIVE INK.
PLATE THRU ALL HOLES WITH COPPER
MIN. PLATING THICKNESS: 1 OZ. EXCEPT
WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/- .003 INCH
WITH RESPECT TO CTR. OF DRILLED PAD.
ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:




Component Side
Demo Circuit 741A Rev3



SIZE	QTY	SYM	PLTD	TOL
10	5	X	YES	+/-0.0
31	3	◇	YES	+/-0.0
94	6	⊗	YES	+/-0.0
35	8	⊗	YES	+/-0.0
70	2	+A	NO	+/-0.0

Fabrication Drawing

APPROVALS			 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INIT	DATE		
CHECK			TITLE: VLDO Linear Regulator	
DESIGN	Rudy B.			
ENGR	TGross		SIZE NONE Demo Circuit 741A REV. 3	
SCALE = NONE			DESIGN #230610	SHT 1 of 1