


REVISIONS			
REV	DESCRIPTION	APPR	DATE

Demo Circuit 1115A

FAB DRAWING




SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-3mil
63	4	X	YES	+/-3mil

NOTES: *UNLESS OTHERWISE SPECIFIED.*

- ARTWORK P/N Demo Circuit 1115A Rev0
- FAB PER IPC-A-600, 2-Layers.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH AND FLAMABILITY RATING: 94 V-2 MINIMUM.

- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI, WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN BOTH SIDES WITH WHITE NON-CONDUCTIVE INK.
- PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +/-3mil WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



FAB DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE 1 +
3 PLACE .005 +
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS				 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900			
INIT	DATE	DRAWN	CHECK				
				DESIGN	Rugle	08/06/06	TITLE: General Purpose Current Sense Amplifier
				ENGR	Jomil	08/06/06	
SCALE - NONE				SIZE	A	Demo Circuit 1115A	REV: 0
				SHT 1 of 1			