





SIZE	QTY	SYM	PLATED	TOL
40	4	+	YES	+/-0.003
15	4	x	YES	+/-0.003
128	2	□	NO	+/-0.003
62	2	◇	NO	+/-0.003
36	16	⊗	YES	+/-0.003
94	2	⊕	YES	+/-0.003

- LAYER 1 (COMPONENT SIDE)
- LAYER 2 (GND)
- LAYER 3 (GND)
- LAYER 4 (SOLDER SIDE)

NOTES : Unless Otherwise Specified

- PCBs ARE TO BE RoHS COMPLIANT
- MATERIAL : FR4 OR EQUIVALENT EPOXY
2 OZ OUTER, 1 OZ INNER COPPER CLAD
 - THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS
 - FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
 - LEAD FREE SOLDER BOTH SIDES.
 - SOLDER MASK OVER BARE COPPER (SMOBC)
 - SOLDER MASK : BOTH SIDES USING GREEN LPI OR EQUIVALENT
 - SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
 - ALL DIMENSIONS ARE IN INCHES
 - SCORING (for production run only)



- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH

Fabrication Drawing

APPROVALS		LINEAR TECHNOLOGY	
DRAWN	INIT	DATE	
CHECK			
DESIGN	Antonio		
ENGR	Akin K.		
SCALE = NONE		DES-23xxxx	
TITLE: LTC4265EDE		Power Device Interface Controller	
SIZE	None	Demo Circuit 1415A	REV. 2
SHT 1 of 1			