

FEATURES

- Low power QVGA imager with logarithmic sensitivity
 - 130dB dynamic range
 - Edge detection and homography analytics algorithm for tracking and counting object motion
- Low power ADSP Blackfin® digital signal processing
 - 512Mb LPDDR SRAM for advanced algorithms
- Image Stabilization
 - Dual axial digital gyroscope, up to $\pm 100^\circ/s$ dynamic range
 - Tri-axial digital accelerometer, up to $\pm 16 g$ dynamic range
- Autonomous operation and data collection
 - Configurable boot-loader installed within flash memory
- Factory calibrated optical focus and alignment
- Conformal coated for environmental mitigation
- Designed to be FCC recognized:
 - FCC CFR 47 Part 15, Subpart B, class B
- Programmable operation and control for custom video analytics firmware
- Secure authentication option available
- USB 2.0 compliant interface for data, supply, ground
- Single-supply: 4.75V-5.25V via ruggedized USB 2.0
- Operating temperature range: -40°C to $+85^\circ\text{C}$
- 10kV ESD interface protection

APPLICATIONS

- Smart City video analytics
- Parking detection
- Machine vision
- Industrial analytics and lighting


GENERAL DESCRIPTION

The [ADIS17001](#) is a low power video analytics camera in a small form factor for interface to USB 2.0 HOST compliant devices including single board computers. It includes a dual axial gyroscope and a tri-axial accelerometer for image stabilization, tilt and impact detection. The [ADIS17001](#) combines industry leading logarithmic sensitivity video imager technology along with digital signal processing and IMU that optimize video performance. Optical factory calibration is performed for each camera for optimum focus and alignment.

The [ADIS17001](#) provides a simple, cost effective method for integrating video sensor, digital signal processing, and IMU into industrial systems, especially when compared with the complexity and investment associated with discrete designs. All optical calibrations are part of the production process at the factory, greatly reducing system-commissioning time. The USB 2.0 and software API provide a simple interface for video collection and configuration control.

The [ADIS17001](#) is a complete camera within a small form factor board using a single USB 2.0 connector interface. The [ADIS17001](#) provides a 110° horizontal field of view (HFOV) lens.

FUNCTIONAL BLOCK DIAGRAM



Rev.PrA

Document Feedback Information furnished by Analog Devices is believed to be accurate and reliable. However, no responsibility is assumed by Analog Devices for its use, nor for any infringements of patents or other rights of third parties that may result from its use. Specifications subject to change without notice. No license is granted by implication or otherwise under any patent or patent rights of Analog Devices. Trademarks and registered trademarks are the property of their respective owners.

ADIS17001* PRODUCT PAGE QUICK LINKS

Last Content Update: 03/15/2017

COMPARABLE PARTS

View a parametric search of comparable parts.

DOCUMENTATION

Data Sheet

- ADIS17001: Low Power, Small Form Factor Video Analytics Camera Preliminary Data Sheet

DESIGN RESOURCES

- ADIS17001 Material Declaration
- PCN-PDN Information
- Quality And Reliability
- Symbols and Footprints

DISCUSSIONS

View all ADIS17001 EngineerZone Discussions.

SAMPLE AND BUY

Visit the product page to see pricing options.

TECHNICAL SUPPORT

Submit a technical question or find your regional support number.

DOCUMENT FEEDBACK

Submit feedback for this data sheet.
