

## MAX25252

# Five-Output ASIL B PMIC with Accurate Temperature Monitoring for Next-Generation Camera Sensors

### General Description

The MAX25252 is a high-efficiency, five-output ASIL B PMIC with three DC-DC converters, and two high-PSRR LDOs, with OV/UV monitoring on all outputs. OUT1 is a 1A high-voltage, synchronous step-down converter operating from power over coax. OUT2 and OUT3 are low voltage synchronous step-down converters and provide a 0.75V to 3.9375V output voltage range. OUT2 and OUT3 can deliver up to 1.7A current respectively for the high-megapixel cameras and high-speed serializers. LDO4 and LDO5 deliver up to 0.4A and 0.9A of current to power the secondary rails of the imager and a serializer. All outputs achieve  $\pm 1.5\%$  output accuracy over load, line, and temperature range. Overvoltage and undervoltage for each output are monitored and their statuses are communicated through RESET and I<sup>2</sup>C.

The device features temperature monitoring with external NTC. The IC accurately measures PCB temperature and flags the temperature warning through RESET.

The device features a 2.1MHz fixed-frequency PWM mode for better noise immunity and load transient response. The 2.1MHz frequency operation allows for the use of all ceramic capacitors and minimizes external components. The programmable spread-spectrum frequency modulation minimizes radiated electromagnetic emissions.

The I<sup>2</sup>C programmable output voltages and sequencing increases flexibility for different image sensors and configurations. Other features include soft-start, overcurrent, and overtemperature protections.

### Applications

- Surround-View Cameras
- Rear-View Cameras
- Side-View Cameras
- Forward-Looking Cameras

### Benefits and Features

- Multiple Functions for Small Size
  - 1A Synchronous High-Voltage Buck Converter
    - Input Voltage Range 3.5V to 22V
    - 2.5V to 5V Output Voltage in 100mV Steps
  - Two Synchronous Low-Voltage Buck Converters
    - Delivers up to 1.7A Current
    - 0.75V to 3.9375V Output Voltage in 12.5mV Steps
  - High-PSRR, Low-Voltage LDO for Camera Sensor
    - Delivers up to 0.4A Current
    - 0.75V to 3.9375V Output Voltage in 12.5mV Steps
  - Low-Voltage LDO
    - Delivers up to 0.9A Current
    - 0.75V to 3.9375V Output Voltage in 12.5mV Steps
  - 2.1MHz Operation
  - RESET Output for OV/UV Detection and Other Diagnostics
  - SUP Voltage OV/UV Indication
- High Precision for ASIL B Applications
  - $\pm 1.5\%$  Output Voltage Accuracy (OUT1-OUT5)
  - $\pm 1\%$  OV/UV Monitoring Accuracy
- High-Precision Temperature Monitoring
  - 12-Bit ADC for Accurate Board Temperature
  - $\pm 0.096\%$  Voltage Measurement Accuracy
- Robust for the Automotive Environment
  - ASIL B Compliant
  - Current-Mode, Forced-PWM Operation
  - Overtemperature and Short-Circuit Protection
  - 5mm x 5mm, 28-Pin Side-Wettable TQFN
  - -40°C to +125°C Automotive Temperature Range
  - AEC-Q100 Qualified

Visit [Web Support](#) to complete the nondisclosure agreement (NDA) required to receive additional product information.

[Ordering Information](#) appears at end of data sheet.

19-101615; Rev 3; 4/26

© 2026 Analog Devices, Inc. All rights reserved. Trademarks and registered trademarks are the property of their respective owners.

One Analog Way, Wilmington, MA 01887 U.S.A. | Tel: 781.329.4700 | © 2026 Analog Devices, Inc. All rights reserved.

Simplified Block Diagram



