



AHEAD OF WHAT'S POSSIBLE™

LT4356-3

Data Sheet Limit Change Comparison

V_{CC} Supply Current Limit Change

- ▶ V_{CC} Supply Current (LT4356H, LT4356MP) max limit to be changed from 40 μA to 50 μA.

BEFORE

LT4356-3

ELECTRICAL CHARACTERISTICS The ● denotes the specifications which apply over the full operating temperature range, otherwise specifications are at T_A = 25°C. V_{CC} = 12V unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
V _{CC}	Operating Voltage Range		● 4		80	V
I _{CC}	V _{CC} Supply Current	V _{SHDN} = Float	●	1	1.5	mA
		V _{SHDN} = 0V, I _{IN+} = 1.3V		7	25	μA
		LT4356C, LT4356I	●	7	30	μA
		LT4356H, LT4356MP	●	7	40	μA

AFTER

LT4356-3

ELECTRICAL CHARACTERISTICS The ● denotes the specifications which apply over the full operating temperature range, otherwise specifications are at T_A = 25°C. V_{CC} = 12V unless otherwise noted.

SYMBOL	PARAMETER	CONDITIONS	MIN	TYP	MAX	UNITS
V _{CC}	Operating Voltage Range		● 4		80	V
I _{CC}	V _{CC} Supply Current	V _{SHDN} = Float	●	1	1.5	mA
		V _{SHDN} = 0V, I _{IN+} = 1.3V		7	25	μA
		LT4356C, LT4356I	●	7	30	μA
		LT4356H, LT4356MP	●	7	50	μA