

Yellow denotes an increase in specification value

Current Data Sheet IDD Limits

ADUM2201, 5.0V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.1	1.5	mA
I _{DD2} - 1Mbps		1.3	1.8	mA
I _{DD1} - 10Mbps		2.6	3.4	mA
I _{DD2} - 10Mbps		3.1	4.0	mA

ADUM2201, 3.0V/3.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.7	1.3	mA
I _{DD2} - 1Mbps		0.8	1.6	mA
I _{DD1} - 10Mbps		1.5	2.1	mA
I _{DD2} - 10Mbps		1.9	2.4	mA

ADUM2201, 5.0V/3.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.1	1.5	mA
I _{DD2} - 1Mbps		0.8	1.6	mA
I _{DD1} - 10Mbps		2.6	3.4	mA
I _{DD2} - 10Mbps		1.9	2.4	mA

ADUM2201, 3.0V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.7	1.3	mA
I _{DD2} - 1Mbps		1.3	1.8	mA
I _{DD1} - 10Mbps		1.5	2.1	mA
I _{DD2} - 10Mbps		3.1	4.0	mA

Revised Data Sheet IDD Limits

ADUM2201, 5.0V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.1	1.6	mA
I _{DD2} - 1Mbps		1.3	1.9	mA
I _{DD1} - 10Mbps		3.1	4.2	mA
I _{DD2} - 10Mbps		3.1	4.0	mA

ADUM2201, 3.3V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.7	1.3	mA
I _{DD2} - 1Mbps		0.8	1.6	mA
I _{DD1} - 10Mbps		1.9	2.5	mA
I _{DD2} - 10Mbps		1.9	2.5	mA

ADUM2201, 5.0V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.1	1.6	mA
I _{DD2} - 1Mbps		0.8	1.6	mA
I _{DD1} - 10Mbps		3.1	4.2	mA
I _{DD2} - 10Mbps		1.9	2.5	mA

ADUM2201, 3.3V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.7	1.3	mA
I _{DD2} - 1Mbps		1.3	1.9	mA
I _{DD1} - 10Mbps		1.9	2.5	mA
I _{DD2} - 10Mbps		3.1	4	mA