

Yellow denotes an increase in specification

Current Data Sheet IDD Limits

ADUM2210, 5.0V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.7	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		1.7	2.8	mA

ADUM2210, 3.0V/3.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.1	1.7	mA

ADUM2210, 5.0V/3.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.7	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		1.1	1.7	mA

ADUM2210, 3.0V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.7	2.8	mA

Revised Data Sheet IDD Limits

ADUM2210, 5.0V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.7	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		3.5	4.8	mA
I _{DD2} - 10Mbps		1.7	2.8	mA

ADUM2210, 3.3V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.1	1.9	mA

ADUM2210, 5.0V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		1.3	1.7	mA
I _{DD2} - 1Mbps		0.7	1.0	mA
I _{DD1} - 10Mbps		3.5	4.8	mA
I _{DD2} - 10Mbps		1.1	1.9	mA

ADUM2210, 3.3V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 1Mbps		0.8	1.3	mA
I _{DD2} - 1Mbps		1.0	1.6	mA
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.7	2.8	mA

Die revision does not effect the IDD performance at 3.3V/5.0V