

Yellow denotes an increase in specification

Current Data Sheet IDD Specifications

ADUM3210W, 5.0V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		1.7	2.8	mA
I _{DD1} - 25Mbps		6.6	9.0	mA
I _{DD2} - 25Mbps		3.8	4.5	mA

ADUM3210W, 3.3V/3.3V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.1	1.7	mA
I _{DD1} - 25Mbps		3.9	5.5	mA
I _{DD2} - 25Mbps		2.4	3.0	mA

ADUM3210W, 5.0V/3.3V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		3.5	4.6	mA
I _{DD2} - 10Mbps		1.1	1.7	mA
I _{DD1} - 25Mbps		6.6	9.0	mA
I _{DD2} - 25Mbps		2.4	3.0	mA

ADUM3210W, 3.3V/5.0V Operation (From:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		2.0	3.2	mA
I _{DD2} - 10Mbps		1.7	2.8	mA
I _{DD1} - 25Mbps		3.9	5.5	mA
I _{DD2} - 25Mbps		3.7	4.5	mA

Revised Data Sheet IDD Specifications

ADUM3210W, 5.0V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		3.5	4.8	mA
I _{DD2} - 10Mbps		2.0	2.8	mA
I _{DD1} - 25Mbps		7.6	9.9	mA
I _{DD2} - 25Mbps		3.8	5.1	mA

ADUM3210W, 3.3V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		2.1	3.2	mA
I _{DD2} - 10Mbps		1.3	1.9	mA
I _{DD1} - 25Mbps		4.6	6.1	mA
I _{DD2} - 25Mbps		2.4	3.4	mA

ADUM3210W, 5.0V/3.3V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		3.5	4.8	mA
I _{DD2} - 10Mbps		1.3	1.9	mA
I _{DD1} - 25Mbps		7.6	9.9	mA
I _{DD2} - 25Mbps		2.4	3.4	mA

ADUM3210W, 3.3V/5.0V Operation (To:)

Specification	Min	Typ	Max	Unit
I _{DD1} - 10Mbps		2.1	3.2	mA
I _{DD2} - 10Mbps		2.0	2.8	mA
I _{DD1} - 25Mbps		4.6	6.1	mA
I _{DD2} - 25Mbps		3.7	5.1	mA