



REVISIONS		
REV	DESCRIPTION	DATE

- NOTES : Unless Otherwise Specified**
1. FAB PER IPC-A-600.
 2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4. 4 OZ. COPPER ON OUTER LAYER, 2 OZ. COPPER ON INNER LAYER, THICKNESS .062 +/- .006 TOTAL OF 6 LAYERS. FLAMABILITY RATING: 94 V-0 MINIMUM .
 3. SIZE: DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
 4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING. HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
 5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN. SILVER IMMERSION BOTH SIDES.
 6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
 7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
 8. SCORING:



SIZE	QTY	SYM	PLTD
15	62	+	PLTD
70	2	X	NPLTD
95	2	□	PLTD
195	2	◇	PLTD
65	2	⊗	PLTD
187	4	⊠	PLTD
25	47	A	PLTD

FAB DRAWING

**UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ±1
2 PLACE ±.01 3 PLACE ±.005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994**

APPROVALS		INIT		DATE	
DRAWN	CHECK				
DESIGN	ENGR	JUNE WU	K. Mathews	12/5/05	12/5/25

LINEAR TECHNOLOGY
1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE: LTC3725EMSE, LTC3726EGN
36V-72Vin Forward Converter

SIZE A **DEMO** DC1031A **REV.** A

SCALE = NONE

SHT 1 of 1