


SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-0.0
94	12	X	YES	+/-0.0
40	19	▭	YES	+/-0.0
15	73	◇	YES	+/-0.0

- ART01 = LAYER 1 (COMPONENT SIDE)
- ART02 = LAYER 2 (GND)
- ART03 = LAYER 3 (GND)
- ART04 = LAYER 4 (SOLDER SIDE)

NOTES: Unless Otherwise Specified:


- PCBS Are To Be RoHS Compliant
- Fab Per IPC-A-600
- Material: Epoxy Fiberglass, NEMA Grade FR-4, 4 Layers
.062 +/- .005 Inch Thickness With
2 OZ. Copper Finished On All Outer Layers,
1 OZ. Copper On All Internal Layers.
Flammability Rating: 94 V-2 Minimum.
- Size: Cut To Dimensions And Tolerances Shown.
- Finish: SMOBC Using Wet Mask, Or LPI Both Sides, Color Green.
Silkscreen Both Sides with White Non-conductive Ink.
- Drilling: Drill Holes Per Schedule. Plate Through
Holes With Copper, .001 Inch Thick Min. All
Hole Sizes Are Specified After Plating.
Hole Location Tolerances Are +/- .003" In Relation To Center.
Do Not Alter Artwork To Add Logo Or Date Code,
You May Modify Pad Size To Meet End Finish.
- Scoring: (Not Required For Prototype Boards)



Fabrication Drawing

APPROVALS

DRAWN	INIT	DATE
CHECK		
DESIGN		
ENGR		



1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408)432-1900

TITLE: LTC3546EUFD, Dual Synchronous, Configurable,
High Switching Frequency Buck Regulator

SIZE	Rev.
NONE	A

SCALE = NONE DESIGN # SHT 1 of 1