


- ART01 = LAYER 1 (COMPONENT SIDE)
ART02 = LAYER 2 (SOLDER SIDE)

NOTES : Unless Otherwise Specified


1. MATERIAL: EPOXY FIBERGLASS, FR-4
 .062 +/- .005 INCH THICKNESS WITH 2 OZ.
 COPPER FINISH ON TWO OUTER LAYERS.
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE
 WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
 SOLDER MASK OVER BARE COPPER (SMOBC)
3. SOLDER MASK : BOTH SIDES USING GREEN LPI OR EQUIVALENT
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.

6. SCORING: (FOR PRODUCTION BOARD)



	SIZE	QTY	SYM	PLTD	TOL
63		10	+	YES	+/-0.003
70		2	X	NO	+/-0.003
10		23	□	YES	+/-0.003
31		9	◇	YES	+/-0.003

Fabrication Drawing

APPROVALS						 1630 McCarthy Blvd. Milpitas, CA 95035 Ph: (408)432-1900	
		INIT	DATE				TITLE: LTC2954CTSS-2
DRAWN							Push Button ON/OFF Controller with uP Interrupt
CHECK							
DESIGN		Antoninok					
ENGR		Dilian R					
				SIZE	NONE	Demo Circuit 1090A	REV. 3
SCALE = NONE				DES-25xxxxx			SHT 1 of 1