



REVISIONS		
REV	APPR	DATE

NOTES: UNLESS OTHERWISE SPECIFIED,

- ARTWORK P/N DC1095A REV 2, 4 LAYER
- FAB PER IPC-A-600
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH ON TWO OUTER LAYERS AND 1 OZ. COPPER ON TWO INTERNAL LAYERS. FLAMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI, WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN COMPONENT SIDE WITH WHITE NON-CONDUCTIVE INK
- PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRIILL: ALL HOLES SHALL BE DRILLED +/-3MIL WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



Linear Tech. Corp.
Demo Circuit 1095A



SIZE	QTY	SYM	PLATED	TOL
187	4	+	YES	+/-3MIL
94	4	X	YES	+/-3MIL
70	2	□	NO	+/-3MIL
8	16	◇	YES	+/-3MIL
31	6	⊗	YES	+/-3MIL

Fabrication Drawing

APPROVALS		TITLE:	
DRAWN	INT	DATE	
CHECK			
DESIGN	Rmb		
ENGR	Dawdc		
		SIZE	NON
		None	Demo Circuit 1095A
		DES-777777	REV. 2
		SCALE = NONE	SHT 1 of 1



LINEAR

TECHNOLOGY

1630 McCarty Blvd,
Milpitas, CA 95035
PH: (408)432-1900

Buck-Boost Synchronous Converter