


SIZE	QTY	SYM	PLATED	TOL
120	2	+	YES	+/-0.0
100	1	X	YES	+/-0.0
40	10	□	YES	+/-0.0
35	21	◇	YES	+/-0.0
47	15	⊗	YES	+/-0.0
125	2	⊠	YES	+/-0.0
65	15	⊕	YES	+/-0.0
70	2	⊖	NO	+/-0.0
187	4	⊙	YES	+/-0.0
10	97	⊔	YES	+/-0.0

FAB Drawing

FAB DRAWING

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600. PCBs ARE TO BE ROHS COMPLIANT.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON OUTER LAYERS.
1 OZ. COPPER FINISH ON INNER LAYERS.
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/--.003 INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR RED
GOLD IMMERSION.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ± 1
2 PLACE ± .01 3 PLACE ± .005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

APPROVALS

DRAWN	INIT	DATE
CHECK		
DESIGN	J. WU	4/3/07
ENGR	M. Guries	4/3/07



TITLE:	LTC4009CUF-2 Three Cell 12.6V@2A Switching Battery Charger
SIZE	A
IDEA	DC1104A
REV.	A

SCALE = NONE

SHT 1 of 1