



L1 - Component Side




SIZE	QTY	SYM	PLATED	TOL
10	392	+	YES	+/-3Mil
187	4	X	YES	+/-3Mil
70	2	□	NO	+/-3Mil
63	3	◇	YES	+/-3Mil
31	3	⊗	YES	+/-3Mil

9. SCORING:



REVISIONS			
REV	DESCRIPTION	APPR	DATE



NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON TOP LAYER.
1 OZ. COPPER FINISH ON REMAINING LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM.
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES +/-0.010
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-3MIL
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. IMPEDANCE CONTROL: 20mils TRACE = 50 OHMS

FABRICATION DRAWING

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE 1 +:
3 PLACE .005 +:
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994



1630 McCarthy Blvd.
Milpitas, CA 95035
PH: (408) 432-1900

TITLE: Differential Driver/Receiver

SIZE A REV. 1

Demo Circuit 1108A

SHT 1 of 1