



Demo Circuit 1117A



SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/-3Mil
63	5	X	YES	+/-3Mil
16	4	□	YES	+/-3Mil

NOTES: UNLESS OTHERWISE SPECIFIED.

- ARTWORK PIN Demo Circuit 1117A Rev0
- FAB PER IPC-A-600, 2Layers.
- MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4 .062 +/- .005 INCH THICKNESS WITH 2 OZ. COPPER FINISH AND FLAMABILITY RATING: 94 V-2 MINIMUM .
- SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN. 0.00 ARE PRIMARY DATUMS.
- BOARD: SELECTIVE PLATED BOARD. SOLDER MASK OVER BARE COPPER, COLOR, GREEN LPI. WHITE TIN IMMERSION (OMIKRON) BOTH SIDES. SILKSCREEN BOTH SIDES WITH WHITE NON-CONDUCTIVE INK. PLATE THRU ALL HOLES WITH COPPER MIN. PLATING THICKNESS: 1 OZ. EXCEPT WHERE PLATING NOT REQUIRED
- DRILL: ALL HOLES SHALL BE DRILLED +3mil WITH RESPECT TO CTR. OF DRILLED PAD. ALL HOLES FINISHED SIZE AFTER PLATING.
- DROP ALL UNUSED PADS ON INNER LAYERS.
- DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
- SCORING:



FAB DRAWING

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE 1 ± 3 PLACE .005 ± INTERPRET DIM AND TOL PER ASME Y14.5M - 1994		APPROVALS		LINEAR TECHNOLOGY 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
		DRAWN	DATE	TITLE: Bi-Directional Current Sense Amplifier	
CHECK	DESIGN	DATE	DATE	SIZE	REV.
ENGR	JWM	03/06/06	03/06/06	A	0
SCALE = NONE				SHT 1 of 1	