



Component Side



SIZE	QTY	SYM	PLTD	TOL
185	4	+	NO	+/-0.003
94	13	X	YES	+/-0.003
70	2	□	NO	+/-0.003
10	101	◇	YES	+/-0.003
31	6	⊗	YES	+/-0.003

## REVISIONS


REV	APPR	DATE
-----	------	------




**NOTES : Unless Otherwise Specified**

1. MATERIAL : FR4 OR EQUIVALENT EPOXY  
2 OZ OUTER, 1 OZ INNER COPPER CLAD  
THICKNESS .062 +/--.006 TOTAL OF 4 LAYERS
2. FINISH : ALL PLATED HOLES .001 MIN. / .0015 MAX. COPPER PLATE  
WHITE TIN IMMERSION (OMIKRON) BOTH SIDES.  
OR LEAD FREE SOLDER  
SOLDER MASK OVER BARE COPPER (SMOBC)
3. SOLDER MASK : BOTH SIDES USING GREEN LPI OR EQUIVALENT
4. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK
5. DO NOT ALTER ARTWORK e.g. TO ADD LOGO, DATE OR TEST CODE.

## 6. SCORING.



# Fabrication Drawing

<h1 style="text-align: center;">APPROVALS</h1>					1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
			TITLE: LTC3850EUF 3.3V/5A and 2.5V/5A REGULATOR		REV. 3	
		INIT	DATE	SIZE	NON	Demo Circuit 1126A
	DRAWN					
	CHECK					
	DESIGN	Antonino				
	ENGR	MikeStriver				
SCALE = NONE				DES-23xxxx		SHT 1 of 1