


Top Side

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON OUTER LAYERS.
1 OZ. COPPER FINISH ON INNER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS SHOWN AND TOLERANCES TOL: +/-0.010.
0.000 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
IMMERSION SILVER SOLDER PLATING
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. SCORING:



Fabrication Drawing

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ± 1
2 PLACE ± .01 3 PLACE ± .005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

SIZE	QTY	SYM	PLTD	TOL
0.07	2	+	NO	+/-0.003
0.095	4	X	YES	+/-0.003
0.01	54	□	YES	+/-0.003
0.065	7	⊗	YES	+/-0.003

APPROVALS

DRAWN	INIT	DATE
CHECK		
DESIGN	Helen	6/19/06
ENGR	Walker Bal	6/19/06



TITLE: LT3477FE+LT3003EMSE, High Current
Multi-String LED Driver with Wide PWM Dimming Range

SIZE	DEM	DC1130A	REV. A
A			
DES-250			

SHEET 1 of 1