



REVISIONS			
REV	DESCRIPTION	APPR	DATE


NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
2 OZ. COPPER FINISH ON OUTER LAYERS.
1 OZ. COPPER FINISH ON INNER LAYERS.
THICKNESS .062 +/- .006 TOTAL OF 4 LAYERS.
FLAMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN.
0.00 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH HOLES WITH COPPER, .001 INCH THICK MIN. ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/- .003 INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
SILVER IMMERSION OR LEAD FREE SOLDER BOTH SIDES.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
8. LAYER 2 AND LAYER 3 ARE IDENTICAL.
9. SCORING:(FOR PRODUCTION BOARD ORDER)



SIZE	QTY	SYM	PLATED	TOL
95	7	+	YES	+/-0.0
35	14	X	YES	+/-0.0
15	53	□	YES	+/-0.0
70	2	◇	NO	+/-0.0
10	6	⊗	YES	+/-0.0

FAB DRAWING

APPROVALS					1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900		
		INIT	DATE	TITLE: LTC3411AEDD 1.25A Monolithic Synchronous Buck Regulator			
DRAWN							
CHECK							
DESIGN	JUNE WU	9/14/06					
ENGR	TOM G.	9/14/06					
				SIZE	DEMO	DC1176A	REV. A
SCALE = NONE				REV 2	SHT 1 of 1		