



REVISION HISTORY			
ECO	REV	DESCRIPTION	DATE
-	1	PRODUCTION	10-20-09

NOTES: UNLESS OTHERWISE SPECIFIED


1. FAB PER IPC-A-600
2. MATERIAL: -EPOXY FIBERGLASS, NEMA GRADE FR-4
-FINISHED THICKNESS TO BE 0.062" +/- .005"
-TOTAL OF 4 LAYERS WITH 2 OZ. CU ON THE
OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
-FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, 0.001" THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-0.003"
IN RELATION TO CENTER
5. FINISH: -SNOB: USING LPT BOTH SIDES; COLOR GREEN.
-GOLD IMMERSION BOTH SIDES.
-FOR SILKSCREEN: TOP SIDE USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED PCB:



Linear Tech. Corp. Component Side
Demo Circuit 1209A



SIZE	QTY	SYM	PLATED	TOL
70	2	+	NO	+/- 3Mil
94	4	X	YES	+/- 3Mil
35	16	□	YES	+/- 3Mil
31	3	◇	YES	+/- 3Mil
10	9	⊗	YES	+/- 3Mil



LAYER CONSTRUCTION

APPROVALS		LINEAR TECHNOLOGY	
PCB DES.	INIT	DATE	DATE
ENG.	Rev'd	10-20-09	10-20-09
Tiger Zhou		Tiger Zhou	
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON ANGLE 1:1 0.00" = 0.01" 0.000" = 0.005" INTERPRET DIM AND TOL PER ASME Y14.5M-1994		1630 MCCARTHY BLVD MILPITAS, CA 95035 PH: (408)432-1900 LTC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
THIRD ANGLE PROJECTION		TITLE: FABRICATION DRAWING 100mA MICROPOWER LOW DROPOUT LINEAR REGULATOR	
DO NOT SCALE DRAWING		SCALE: NONE	SCALE: NONE
DO NOT SCALE DRAWING		FILENAME: DC1209A-1.PCB	FILENAME: DC1209A-1.PCB
DO NOT SCALE DRAWING		SIZE A	SIZE A
DO NOT SCALE DRAWING		IC NO. LT3060EDC	IC NO. LT3060EDC
DO NOT SCALE DRAWING		REV. 1	REV. 1
DO NOT SCALE DRAWING		DEMO CIRCUIT 1209A	DEMO CIRCUIT 1209A
DO NOT SCALE DRAWING		SHT 1 of 1	SHT 1 of 1