





NOTES: UNLESS OTHERWISE SPECIFIED

1. FAB PER IPC-A-600
2. MATERIAL: - EPOXY FIBERGLASS, NEMA GRADE FR-4
 - FINISHED THICKNESS TO BE 0.062" +/- .005"
 - TOTAL OF 6 LAYERS WITH 2 OZ. CU ON THE OUTER LAYERS AND 1 OZ. CU ON THE INNER LAYERS.
 - FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: CUT TO DIMENSIONS AND TOLERANCES SHOWN.
0.00" ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE PLATE THROUGH HOLES WITH COPPER, 0.001" THICK MIN.
ALL HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/-0.003"
IN RELATION TO CENTER
5. FINISH: -SMOBC USING LPT BOTH SIDES, COLOR GREEN.
 - GOLD IMMERSION BOTH SIDES.
 - FOR SILKSCREEN: BOTH SIDES USE WHITE NON-CONDUCTIVE INK.
6. DO NOT ALTER ARTWORK e.g. TO ADD LOGO OR DATE CODE.
PAD SIZE CAN BE MODIFIED TO MEET END FINISH.
7. PCBs ARE TO BE RoHS COMPLIANT.
8. SCORING FOR PANELIZED POB:



SIZE	QTY	SYM	PLATED	TOL
187	4	+	YES	+/- .001
70	2	X	NO	+/- .001
94	9	□	YES	+/- .001
205	4	◇	YES	+/- .001
8	51	⊗	YES	+/- .001
18	48	⊗	YES	+/- .001
10	4	⊕	YES	+/- .001
31	10	⊕	YES	+/- .001

UNLESS OTHERWISE SPECIFIED		APPROVALS		LINEAR TECHNOLOGY		1630 MCCARTHY BLVD MILLPITAS, CA 95035 PH: (408)552-1900 WWW.LINEAR.COM E-TC CONFIDENTIAL- FOR CUSTOMER USE ONLY	
DIMENSIONS ARE IN INCHES		PCB DES.	✕B				
TOLERANCES:		APP ENG.	CHARLIE Z.				
0.XX" = +0.01"							
0.XXX" = +0.005"							
INTERPRET DIM AND TOL PER ASME Y14.5M-1994							
THIRD ANGLE PROJECTION							
				SIZE	IC NO.	LTC3852EUDD	REV
				N/A		DEMO CIRCUIT 1270A	3
		SCALE = NONE		FILENAME:		DC1270A-3-PCB	
						SHT 1 OF 1	