


SIZE	QTY	SYM	PLTD	TOL
0.187	4	+	NO	+/-0.003
0.07	2	X	NO	+/-0.003
0.095	4	□	YES	+/-0.003
0.025	76	◇	YES	+/-0.003
0.01	171	⊗	YES	+/-0.003

UNLESS OTHERWISE SPECIFIED
DIMENSIONS ARE IN INCHES
TOLERANCES ON ANGLE ± 1
2 PLACE ±.01 3 PLACE ±.005
INTERPRET DIM AND TOL
PER ASME Y14.5M - 1994

REVISIONS		
REV	DESCRIPTION	DATE

NOTES : Unless Otherwise Specified

1. FAB PER IPC-A-600.
2. MATERIAL: EPOXY FIBERGLASS, NEMA GRADE FR-4.
4 OZ. COPPER FINISH ON OUTER LAYERS.
2 OZ. COPPER FINISH ON INNER LAYERS.
THICKNESS .062 +/--.006 TOTAL OF 6 LAYERS.
FLAMMABILITY RATING: 94 V-0 MINIMUM .
3. SIZE: DIMENSIONS AND TOLERANCES SHOWN. TOL: +/-0.005
0.000 ARE PRIMARY DATUMS.
4. DRILLING: DRILL HOLES PER SCHEDULE. PLATE THROUGH
HOLES WITH COPPER, .001 INCH THICK MIN. ALL
HOLE SIZES ARE SPECIFIED AFTER PLATING.
HOLE LOCATION TOLERANCES ARE +/--.003
INCH IN RELATION TO CENTER
5. FINISH: SMOBC USING LPI BOTH SIDES COLOR GREEN.
IMMERSION GOLD PLATING.
6. SILKSCREEN : USING WHITE NON-CONDUCTIVE EPOXY INK.
7. DO NOT ALTER ARTWORK TO ADD LOGO OR DATE CODE.
BUT YOU MAY MODIFY PAD SIZE TO MEET END FINISH.
8. PCBs ARE TO BE RoHS COMPLIANT.
9. SCORING:



Fabrication Drawing

APPROVALS <table border="1"> <tr> <th>DRAWN</th> <th>INT</th> <th>DATE</th> </tr> <tr> <td>CHECK</td> <td></td> <td></td> </tr> <tr> <td>DESIGN</td> <td>Helen</td> <td>10/9/07</td> </tr> <tr> <td>ENGR</td> <td>David B.</td> <td>10/9/07</td> </tr> </table>		DRAWN	INT	DATE	CHECK			DESIGN	Helen	10/9/07	ENGR	David B.	10/9/07	LINEAR TECHNOLOGY 1630 McCarthy Blvd. Milpitas, CA 95035 PH: (408)432-1900	
DRAWN	INT	DATE													
CHECK															
DESIGN	Helen	10/9/07													
ENGR	David B.	10/9/07													
TITLE: LTC3725EMSE, LTC3726EGN 9V-36Vin Forward Converter		SIZE A DEMO DC1300A REV. A													
SCALE = NONE		DES SHT 1 of 1													